

Ceramic Low Pass Filter

LFCN-6400+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
40	0.08	0.02	0.09	42.89	50.93	40.90	43.65	55.42	41.63
100	0.01	0.05	0.04	42.36	48.72	39.50	41.06	45.96	39.51
200	0.01	0.07	0.04	40.24	44.86	42.22	39.80	42.89	42.04
400	0.03	0.09	0.09	39.86	40.07	31.66	39.18	40.58	31.13
500	0.04	0.09	0.09	39.48	38.21	32.12	46.34	39.76	32.12
600	0.05	0.10	0.11	37.35	36.67	32.00	40.82	37.52	32.22
800	0.06	0.13	0.14	34.03	33.63	30.51	35.10	34.08	30.11
1000	0.07	0.14	0.15	30.90	31.09	29.61	31.92	31.87	29.89
2000	0.12	0.23	0.25	23.21	22.94	22.54	23.47	23.22	22.95
3000	0.20	0.33	0.36	17.95	18.01	19.27	17.93	18.07	19.22
4000	0.26	0.41	0.55	16.45	16.39	15.17	16.39	16.53	15.42
5000	0.27	0.44	0.55	21.22	21.46	21.74	21.00	21.27	21.27
5200	0.28	0.45	0.56	24.24	25.14	25.10	23.00	24.39	24.34
5500	0.36	0.54	0.68	49.88	34.32	29.26	33.21	43.41	38.09
6000	0.57	0.77	0.97	21.78	20.16	18.76	22.11	20.28	18.94
6400	0.81	1.10	1.27	16.33	15.81	15.38	16.00	15.08	14.35
7000	1.39	1.70	1.97	14.74	15.38	15.94	14.68	15.58	16.07
7100	1.59	2.01	2.33	13.49	13.51	13.02	15.03	15.27	15.17
7200	2.07	2.58	3.11	10.58	10.03	9.41	12.77	12.28	11.59
7300	3.12	3.95	4.70	7.05	6.58	6.26	8.67	8.11	7.74
7350	4.05	4.94	5.87	5.31	5.05	4.90	6.78	6.45	6.12
7400	5.03	6.06	7.10	4.07	3.95	3.92	5.21	5.07	4.87
7500	8.42	9.65	11.07	2.23	2.37	2.54	3.09	3.19	3.16
7600	12.65	14.14	15.81	1.29	1.51	1.74	1.96	2.13	2.16
7680	17.09	18.94	20.88	0.96	1.18	1.41	1.50	1.69	1.73
7770	23.28	25.61	29.25	0.71	0.92	1.14	1.23	1.44	1.44
7800	26.00	29.00	33.03	0.66	0.86	1.08	1.12	1.31	1.30
8000	32.69	31.26	30.31	0.44	0.60	0.76	0.90	1.04	1.04
8300	27.29	28.02	28.45	0.30	0.44	0.50	0.73	0.90	0.87
9000	42.06	43.47	44.03	0.35	0.43	0.43	0.52	0.87	1.04
10000	35.10	33.53	33.18	0.61	0.82	1.03	0.50	0.87	1.26
10100	33.55	32.90	31.75	0.69	0.89	1.13	0.49	0.88	1.26
10200	32.38	32.22	31.00	0.69	0.88	1.15	0.45	0.83	1.28
10400	30.58	30.31	29.53	0.75	0.94	1.24	0.47	0.85	1.19
10500	29.95	29.16	28.72	0.81	1.01	1.27	0.46	0.84	1.16
11000	25.82	26.02	26.33	0.96	1.11	1.28	0.54	0.76	1.00
12000	21.37	21.59	22.92	1.02	1.17	1.36	0.78	0.82	0.82
12500	21.16	20.98	22.36	1.01	1.28	1.57	0.89	0.93	0.97
13000	19.79	19.24	19.82	0.87	1.27	1.61	1.07	1.08	1.18
14000	18.87	17.67	17.15	1.15	1.67	2.38	1.46	1.53	1.68
15000	17.53	16.97	16.53	1.82	1.99	2.66	1.96	2.19	2.10
17000	17.57	16.83	19.34	1.69	1.94	1.46	1.79	2.67	2.88
18000	21.92	18.93	20.17	0.97	1.55	1.50	0.94	2.08	3.10
20000	17.16	17.15	16.44	1.27	1.08	1.08	0.68	0.46	0.83

REV. X1
LFCN-6400+
080320
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

