

Ceramic Low Pass Filter

LFCN-800+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
10	0.05	0.06	0.07	40.02	46.06	46.03	45.64	46.06	46.85
50	0.08	0.10	0.11	35.81	36.49	36.42	38.06	38.48	38.21
100	0.10	0.14	0.15	28.71	28.92	29.04	28.67	28.83	28.85
765	0.58	0.73	0.84	18.19	18.11	18.13	17.84	17.75	17.74
800	0.69	0.85	0.99	15.40	15.34	15.31	15.39	15.27	15.24
840	0.92	1.09	1.25	12.53	12.43	12.33	12.46	12.33	12.23
970	2.92	3.26	3.62	4.79	4.73	4.65	4.79	4.70	4.60
990	3.49	3.87	4.29	4.01	3.95	3.86	3.99	3.94	3.85
1030	4.93	5.38	5.84	2.75	2.74	2.73	2.76	2.77	2.71
1140	9.97	10.54	11.15	1.00	1.08	1.12	1.02	1.06	1.10
1235	14.90	15.51	16.14	0.53	0.62	0.69	0.50	0.61	0.65
1275	16.98	17.62	18.26	0.44	0.53	0.61	0.42	0.50	0.54
1330	19.86	20.50	21.21	0.36	0.44	0.50	0.34	0.43	0.47
1350	20.93	21.58	22.30	0.32	0.42	0.48	0.30	0.39	0.44
1400	23.58	24.29	25.00	0.28	0.36	0.43	0.28	0.36	0.40
1420	24.69	25.42	26.14	0.26	0.34	0.41	0.26	0.33	0.39
1500	29.21	30.05	30.92	0.24	0.33	0.39	0.22	0.28	0.33
1580	34.58	35.62	36.69	0.20	0.30	0.34	0.19	0.27	0.30
1635	39.05	40.35	41.74	0.20	0.29	0.33	0.17	0.25	0.29
1675	43.18	45.09	47.10	0.18	0.27	0.32	0.17	0.24	0.29
1700	46.61	49.31	51.99	0.16	0.25	0.30	0.17	0.25	0.29
1735	54.91	60.33	62.84	0.18	0.26	0.31	0.15	0.24	0.29
1785	55.87	52.35	49.66	0.17	0.26	0.31	0.15	0.23	0.27
1825	48.20	46.52	45.29	0.18	0.25	0.31	0.14	0.22	0.25
2000	39.24	39.14	38.63	0.15	0.24	0.30	0.14	0.22	0.25
2500	33.99	33.92	33.86	0.12	0.21	0.29	0.12	0.20	0.24
3000	31.55	31.57	31.83	0.09	0.20	0.30	0.13	0.21	0.27
3500	29.88	30.42	30.11	0.11	0.25	0.38	0.11	0.20	0.29
4000	28.95	29.19	29.16	0.09	0.24	0.36	0.11	0.22	0.33
4500	27.66	27.52	27.72	0.12	0.28	0.43	0.18	0.33	0.41
5000	24.84	25.04	25.92	0.25	0.41	0.56	0.24	0.40	0.55
5500	23.28	23.65	24.15	0.28	0.43	0.58	0.28	0.44	0.56
6000	21.82	22.05	22.36	0.35	0.50	0.70	0.36	0.52	0.68
6500	20.66	20.83	21.01	0.30	0.52	0.71	0.29	0.50	0.68
7000	19.33	19.38	19.08	0.47	0.63	0.79	0.35	0.50	0.69
7500	17.70	17.53	17.28	0.50	0.74	0.87	0.37	0.58	0.75
8000	15.52	15.22	14.72	0.70	0.93	1.04	0.60	0.82	1.11
8880	7.09	7.27	8.45	3.86	6.71	7.44	3.05	4.40	6.19
9130	13.60	15.23	12.02	3.00	2.81	3.46	3.71	2.89	3.15
9420	5.02	4.90	5.81	9.15	11.49	7.78	7.46	8.50	6.39
10000	10.38	11.11	11.47	1.31	1.54	1.80	1.32	1.49	1.63

REV. X1
LFCN-800+
070923
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

