

Low Pass Filter

LPF-EDU1019

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.03	0.16	34.67	0.03	598.40
0.30	0.20	35.31	0.05	620.19
0.60	0.38	16.94	0.07	631.24
0.70	0.47	15.94	0.09	630.93
0.88	0.62	22.62	0.12	635.99
0.97	0.96	22.93	0.18	643.23
1.00	1.23	20.04	0.20	645.52
1.05	2.48	10.66	0.25	654.02
1.07	3.20	8.28	0.30	669.95
1.08	4.12	6.32	0.35	678.92
1.12	7.56	3.03	0.40	697.08
1.15	10.76	1.86	0.45	717.61
1.17	13.04	1.41	0.50	733.75
1.20	16.57	1.02	0.55	758.77
1.25	22.54	0.71	0.60	784.12
1.30	28.58	0.58	0.65	819.50
1.37	37.32	0.48	0.70	864.35
1.41	42.67	0.45	0.75	928.94
1.46	50.07	0.42	0.80	1011.52
10.00	81.48	0.26	0.82	1053.43
100.00	93.07	0.16	0.84	1093.63
500.00	77.98	0.24	0.86	1146.15
1000.00	60.49	0.40	0.87	1172.08
1200.00	54.66	0.65	0.88	1186.86