

Metal Shield Low Pass Filter

LPF-EDU1662

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.3	0.13	36.61	0.3	12.28
25.0	0.25	35.32	1.0	13.15
40.0	0.35	24.89	4.0	13.40
60.0	0.65	21.93	8.0	13.21
65.0	0.79	27.05	10.0	13.24
72.0	1.72	12.60	13.0	13.29
74.0	3.33	6.40	15.0	13.13
76.0	6.80	2.99	20.0	13.57
79.0	14.25	1.31	23.0	13.87
83.0	24.64	0.84	25.0	14.02
86.0	32.35	0.71	27.0	14.20
90.0	43.20	0.61	30.0	14.49
93.0	53.02	0.57	32.0	14.75
98.0	65.23	0.50	36.0	15.10
186.0	70.65	0.18	39.0	15.65
300.0	80.52	0.11	41.0	15.99
375.0	85.26	0.10	45.0	16.90
445.0	79.92	0.09	48.0	17.67
600.0	75.31	0.09	50.0	18.31
700.0	75.80	0.10	54.0	19.67
850.0	73.72	0.13	58.0	21.52
900.0	72.86	0.11	60.0	23.04
950.0	76.23	0.13	63.0	25.43
1000.0	74.10	0.13	65.0	27.69



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



REV. X1
LPF-EDU1662
URJ
120719
Page 1 of 1