

Low Noise Amplifier

MAN-1HLN

Typical Performance Data

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR IN (:1) 12V	VSWR OUT (:1) 12V	NOISE FIGURE (dB) 12V	Pout at 1dB Comp. (dBm) 12V
	11V	12V	12.5V	11V	12V	12.5V				
10.0	12.42	12.46	12.48	4.20	4.20	4.20	1.41	1.20	3.91	17.02
19.3	12.29	12.37	12.39	4.20	4.30	4.20	1.25	1.12	3.87	17.33
46.5	12.28	12.35	12.36	4.10	4.10	4.10	1.19	1.08	3.86	17.41
111.8	12.16	12.22	12.23	4.20	4.30	4.30	1.17	1.12	4.07	17.42
198.5	12.13	12.19	12.20	4.20	4.20	4.20	1.17	1.09	4.14	17.29
248.7	12.01	12.06	12.06	4.30	4.40	4.40	1.17	1.14	3.93	17.27
311.5	11.88	11.90	11.91	4.30	4.40	4.30	1.16	1.20	3.97	17.23
374.4	11.68	11.71	11.73	4.40	4.40	4.60	1.18	1.16	4.03	17.29
437.2	11.53	11.57	11.58	4.50	4.50	4.50	1.17	1.28	4.07	17.35
500.0	11.27	11.29	11.32	4.80	4.80	4.70	1.19	1.23	4.13	17.38

REV. X1
MAN-1HLN
060912
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

