

Fixed Attenuator, DC Passing

NAT-10DC+

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	FEMALE RETURN LOSS (dB)	MALE RETURN LOSS (dB)
200	10.30	20.51	21.87
300	10.06	20.91	22.33
400	9.97	21.11	22.29
450	9.94	21.11	22.18
500	9.93	21.19	22.01
550	9.92	21.19	21.77
600	9.90	21.21	21.56
650	9.91	21.19	21.39
700	9.91	21.24	21.17
750	9.91	21.18	20.91
800	9.91	21.16	20.69
850	9.90	21.18	20.42
900	9.90	21.10	20.22
950	9.90	21.07	19.97
1000	9.90	21.00	19.74
1050	9.90	20.95	19.52
1100	9.91	20.83	19.28
1150	9.92	20.75	19.07
1200	9.92	20.62	18.89
1250	9.93	20.53	18.66
1300	9.93	20.37	18.50
1350	9.94	20.22	18.32
1400	9.95	20.04	18.12
1450	9.96	19.89	17.97
1500	9.96	19.72	17.78
1550	9.98	19.51	17.63
1600	9.97	19.29	17.48
1650	9.99	19.05	17.34
1700	10.00	18.80	17.20
1750	10.01	18.55	17.03
1800	10.02	18.26	16.94
1850	10.04	17.98	16.79
1900	10.07	17.72	16.65
1950	10.07	17.40	16.54
2000	10.10	17.15	16.41
2100	10.16	16.50	16.18
2200	10.21	15.89	15.98
2300	10.31	15.23	15.81
2400	10.40	14.62	15.62
2500	10.48	14.06	15.53

REV. X1
NAT-10DC+
061109
Page 1 of 1



IF/Rf MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

