

Fixed Attenuator, DC Passing

NAT-10DC-1A+

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	FEMALE RETURN LOSS (dB)	MALE RETURN LOSS (dB)
600	10.38	19.08	19.73
650	10.03	21.66	23.13
750	9.81	22.12	24.29
900	9.80	20.44	23.13
1200	9.85	17.95	20.44
1350	9.86	16.98	19.73
1500	9.88	16.54	19.40
1650	9.92	16.13	19.08
1800	9.92	15.94	18.78
1950	9.90	15.75	18.49
2100	9.96	15.94	18.22
2250	9.97	16.13	18.22
2500	9.93	16.98	18.49
2800	9.97	18.78	19.08
3100	10.02	21.23	19.73
3250	10.04	22.61	20.44
3400	10.07	24.29	21.66
3700	10.16	25.66	24.94
3850	10.22	24.29	29.42
4000	10.33	22.61	40.09

REV. X1
NAT-10DC-1A+
070329
Page 1 of 1



IF/Rf MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

