

Coaxial Low Pass Filter

NLP-1.9+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.3	0.08	28.87	0.3	344.640
0.4	0.09	26.02	0.4	344.640
0.5	0.11	23.65	0.5	345.930
1.0	0.26	16.66	1.0	357.940
1.5	0.34	18.62	1.5	394.620
2.0	0.50	23.42	2.0	487.760
2.5	3.44	4.72	2.5	771.800
3.0	18.13	0.57	2.8	451.460
3.5	30.68	0.35	2.9	357.210
4.0	40.85	0.29	3.2	204.790
10.0	72.35	0.18	3.3	178.270
100.0	86.81	0.17	3.4	156.070
500.0	66.03	0.31	3.5	140.150
1000.0	52.40	5.78	3.6	124.630
1500.0	107.38	0.56	3.7	110.340
2000.0	63.57	1.17	3.9	97.210
2500.0	49.50	6.01	4.0	89.080
3000.0	60.61	3.14	500.0	3.960
3500.0	34.58	2.23	1000.0	1.970

REV. X1
NLP-1.9+
080710
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

