

Coaxial Low Pass Filter (Flat Time Delay)

NBLP-1870

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.01	47.20	10.0	0.347
152.3	0.05	22.60	152.3	0.346
433.0	0.22	14.10	290.8	0.345
571.6	0.36	11.60	433.0	0.344
710.1	0.53	9.80	571.6	0.344
850.0	0.73	8.30	710.1	0.343
1002.1	0.96	7.20	850.0	0.342
1582.4	2.28	4.00	1002.1	0.343
1870.0	3.21	3.10	1290.4	0.346
2001.7	3.65	2.80	1582.4	0.348
2499.6	5.91	1.60	1870.0	0.345
2997.5	9.36	0.70	2001.7	0.350
3244.6	11.63	0.50	2248.8	0.355
3491.7	13.38	0.30	2499.6	0.347
3740.0	15.60	0.30	2746.7	0.345
4000.8	17.72	0.30	2997.5	0.309
4289.1	20.35	0.30	3244.6	0.308
4573.6	23.49	0.30	3491.7	0.291
4715.9	25.12	0.30	3740.0	0.282
4858.2	26.62	0.20	4000.8	0.287
5000.0	28.10	0.30	4143.1	0.295
5011.7	28.25	0.30	4289.1	0.281
5176.4	30.15	0.20	4431.4	0.262
5341.1	32.09	0.20	4573.6	0.254
5505.8	34.13	0.20	4715.9	0.254
5670.6	36.22	0.20	4858.2	0.249
5752.9	37.22	0.20	5000.0	0.238
5835.3	37.22	0.20	5011.7	0.245
5917.6	39.23	0.20	5094.0	0.258
6000.0	39.53	0.20	5176.4	0.243

REV. X1
NBLP-1870
060724
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

