

Coaxial Low Pass Filter

NLP-1000+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.92	23.38	10.0	5.110
100.0	0.16	28.91	100.0	1.120
200.0	0.23	26.51	200.0	1.000
300.0	0.26	29.36	300.0	1.110
400.0	0.30	71.14	400.0	1.130
500.0	0.30	29.89	500.0	1.170
600.0	0.38	28.68	600.0	1.240
700.0	0.42	25.94	700.0	1.380
800.0	0.53	19.73	800.0	1.530
900.0	0.70	19.74	900.0	2.040
1000.0	3.96	3.73	1000.0	2.160
1100.0	12.94	0.82	1100.0	1.360
1200.0	21.70	0.43	1200.0	0.860
1300.0	29.24	0.35	1300.0	0.660
1400.0	35.71	0.30	1400.0	0.550
1450.0	38.92	0.31	1450.0	0.500
1500.0	41.71	0.28	1500.0	0.490
2000.0	61.41	0.27	2000.0	0.340
2500.0	74.54	0.30	2500.0	0.500
3000.0	79.25	0.42	3000.0	14.020

REV. X1
NLP-1000+
060925
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

