

Coaxial Low Pass Filter (Flat Time Delay)

NBLP-39+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.02	35.50	1.0	8.012
9.0	0.14	17.00	5.0	8.243
12.0	0.23	14.30	9.0	7.823
16.0	0.38	11.60	12.0	8.199
20.0	0.60	9.40	16.0	8.305
23.0	0.82	8.10	20.0	8.466
24.0	0.91	7.70	23.0	8.623
34.0	2.11	4.50	24.0	8.392
39.0	2.95	3.40	29.0	8.899
40.0	3.14	3.20	34.0	8.378
51.0	5.48	1.90	39.0	8.392
62.0	8.15	1.20	40.0	8.247
69.0	9.69	1.00	46.0	7.722
73.0	11.00	0.80	51.0	7.336
78.0	12.33	0.70	57.0	6.804
79.0	12.60	0.70	62.0	6.487
90.0	15.56	0.50	68.0	6.306
101.0	18.53	0.40	73.0	5.277
107.0	20.14	0.30	78.0	5.124
112.0	21.46	0.30	79.0	5.489
117.0	22.76	0.30	85.0	5.101
118.0	23.02	0.30	90.0	4.784
132.0	26.55	0.20	96.0	4.054
146.0	29.88	0.20	101.0	3.996
159.0	32.80	0.10	107.0	3.275
173.0	35.76	0.10	112.0	3.856
180.0	37.17	0.10	117.0	2.547
187.0	38.55	0.10	118.0	2.738
194.0	39.89	0.10	125.0	2.216
200.0	41.00	0.10	132.0	2.576

REV. X1
NBLP-39+
060724
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

