

Coaxial Low Pass Filter

NLP-15+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.3	0.05	36.33	0.3	52.410
1.0	0.07	26.83	1.0	52.030
5.0	0.14	22.22	5.0	53.290
10.0	0.31	16.53	10.0	60.070
15.0	0.52	18.51	15.0	85.120
20.0	16.66	0.44	20.0	54.210
21.0	21.17	0.31	21.0	39.360
22.0	25.32	0.25	22.0	30.210
24.0	32.83	0.18	24.0	19.920
25.0	36.32	0.17	25.0	16.880
27.0	43.03	0.15	27.0	12.400
30.0	53.65	0.12	30.0	7.800
40.0	60.98	0.09	40.0	6.900
50.0	60.02	0.08	50.0	2.050
60.0	60.91	0.07	60.0	1.770
70.0	61.99	0.07	70.0	1.450
80.0	62.99	0.07	80.0	0.290
90.0	63.94	0.08	90.0	0.510
150.0	67.69	0.08	150.0	1.650
300.0	72.04	0.08	300.0	1.470
500.0	71.82	0.08	500.0	4.150
1500.0	50.84	0.83	1500.0	0.730
2000.0	59.88	1.81	2000.0	0.180
3000.0	54.76	0.74	3000.0	0.320

REV. X1
NLP-15+
060925
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

