

Coaxial Low Pass Filter

NLP-2400+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.01	55.15	10.0	0.520
125.3	0.04	42.47	125.3	0.530
240.5	0.06	40.19	240.5	0.530
355.8	0.07	39.56	355.8	0.530
471.1	0.09	35.62	471.1	0.530
586.3	0.11	30.29	586.3	0.540
816.8	0.15	22.41	816.8	0.550
1047.4	0.22	17.59	1047.4	0.560
1277.9	0.29	15.33	1277.9	0.570
1508.4	0.30	15.99	1508.4	0.600
1738.9	0.29	19.02	1738.9	0.650
1969.5	0.34	18.76	1969.5	0.730
2200.0	0.40	20.98	2200.0	0.860
2400.0	2.33	5.06	2400.0	1.120
2775.0	15.86	0.35	2775.0	0.570
3150.0	28.00	0.22	3150.0	0.390
3575.0	39.27	0.17	3575.0	0.330
4000.0	48.63	0.10	4000.0	0.280
5000.0	65.70	0.31	5000.0	0.430
6000.0	63.98	0.08	6000.0	0.490

REV. X1
NLP-2400+
070530
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

