

# Type-N/BNC Adaptenuator

# NF-BF-6

## Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	BNC-FEMALE RETURN LOSS (dB)	N-FEMALE RETURN LOSS (dB)
1	6.00	46.06	46.06
5	5.97	46.06	46.06
10	5.97	46.06	46.06
50	5.97	46.06	46.06
100	6.01	46.06	46.06
500	6.04	32.26	34.15
1000	6.08	32.26	28.30
1500	6.08	36.61	28.30
1700	6.12	36.61	29.42
2000	6.14	36.61	30.71

REV. X1  
NF-BF-6  
061113  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

