

Type-N/BNC Adaptenuator

NF-BM-10

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	BNC-MALE RETURN LOSS (dB)	N-FEMALE RETURN LOSS (dB)
1	10.01	46.06	46.06
5	10.03	46.06	46.06
10	10.03	46.06	46.06
50	10.02	46.06	46.06
100	10.02	46.06	46.06
500	10.06	46.06	40.09
1000	10.09	36.61	36.61
1500	10.05	32.26	30.71
1700	10.08	29.42	30.71
2000	10.08	27.32	26.44

REV. X1
NF-BM-10
061113
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

