

Coaxial Low Pass Filter

NLP-550+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.31	32.48	10.0	1.290
50.0	0.38	40.70	50.0	1.640
100.0	0.15	41.08	100.0	1.660
200.0	0.21	24.92	200.0	1.700
250.0	0.28	19.63	250.0	1.760
300.0	0.36	17.62	300.0	1.830
350.0	0.39	18.11	350.0	1.940
400.0	0.40	20.49	400.0	2.100
450.0	0.46	18.49	450.0	2.290
500.0	0.61	15.55	500.0	2.620
550.0	0.79	15.30	550.0	3.590
600.0	4.13	3.42	600.0	3.850
700.0	19.51	0.46	700.0	1.350
750.0	26.08	0.30	750.0	0.990
800.0	31.97	0.26	800.0	0.810
850.0	37.06	0.23	850.0	0.700
1000.0	50.49	0.22	1000.0	0.510
1500.0	71.89	0.25	1500.0	0.420
2000.0	72.94	0.32	2000.0	0.260
2500.0	68.77	0.33	2500.0	0.240
3000.0	72.43	0.36	3000.0	0.250

REV. X1
NLP-550+
070603
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

