

# Coaxial Low Pass Filter

# NLP-750+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.02	40.04	10.0	1.290
50.0	0.07	25.84	50.0	1.240
91.0	0.11	21.43	91.0	1.260
131.0	0.15	19.25	131.0	1.270
172.0	0.18	18.23	172.0	1.270
213.0	0.20	18.12	213.0	1.280
253.0	0.21	18.90	253.0	1.300
294.0	0.21	20.66	294.0	1.330
375.0	0.23	27.94	375.0	1.400
416.0	0.25	28.88	416.0	1.440
456.0	0.28	25.61	456.0	1.490
497.0	0.31	23.58	497.0	1.550
537.0	0.35	22.80	537.0	1.620
578.0	0.39	22.40	578.0	1.710
619.0	0.43	22.02	619.0	1.840
659.0	0.50	21.19	659.0	2.020
700.0	0.64	18.02	700.0	2.340
724.0	0.86	13.88	724.0	2.600
732.0	0.99	12.40	732.0	2.680
741.0	1.18	10.79	741.0	2.790
747.0	1.34	9.76	747.0	2.850
781.0	2.95	5.08	781.0	2.970
791.0	3.69	4.10	791.0	2.910
799.0	4.36	3.45	799.0	2.820
822.0	6.63	2.13	822.0	2.480
862.0	11.17	1.07	862.0	1.860
903.0	15.89	0.66	903.0	1.410
944.0	20.34	0.50	944.0	1.120
949.0	20.86	0.49	949.0	1.090
959.0	21.89	0.46	959.0	1.050
984.0	24.41	0.42	984.0	0.970
1020.0	27.86	0.37	1020.0	0.850
1060.0	31.45	0.34	1060.0	0.750
1100.0	34.87	0.32	1100.0	0.670
1140.0	38.13	0.30	1140.0	0.620
1170.0	40.46	0.30	1170.0	0.580
1180.0	41.20	0.30	1180.0	0.570
1220.0	44.18	0.29	1220.0	0.530
1260.0	47.02	0.28	1260.0	0.510
1300.0	49.74	0.28	1300.0	0.480
1350.0	53.00	0.28	1350.0	0.490
1390.0	55.49	0.28	1390.0	0.450
1430.0	57.82	0.28	1430.0	0.440
1470.0	60.03	0.28	1470.0	0.540
1510.0	62.18	0.29	1510.0	0.440
1550.0	64.14	0.29	1550.0	0.270
1590.0	65.89	0.29	1590.0	0.380
1630.0	67.42	0.30	1630.0	0.350
1670.0	68.53	0.30	1670.0	0.490
1710.0	70.05	0.30	1710.0	0.170
1750.0	71.00	0.31	1750.0	0.490
1790.0	71.54	0.31	1790.0	0.170
1830.0	72.16	0.31	1830.0	0.790
1950.0	72.55	0.33	1950.0	1.220
2000.0	72.63	0.33	2000.0	0.330

REV. X1  
NLP-750+  
080713  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

