

Type-N/BNC Adaptenuator

NM-BF-6

Typical Performance Data

| FREQUENCY (MHz) | ATTENUATION (dB) | BNC-FEMALE RETURN LOSS (dB) | N-MALE RETURN LOSS (dB) |
|--------------------|---------------------|-----------------------------------|-------------------------------|
| 1 | 5.98 | 46.06 | 46.06 |
| 5 | 5.98 | 46.06 | 46.06 |
| 10 | 6.00 | 46.06 | 46.06 |
| 50 | 6.00 | 46.06 | 46.06 |
| 100 | 6.01 | 46.06 | 46.06 |
| 500 | 6.07 | 34.15 | 32.26 |
| 1000 | 6.12 | 29.42 | 27.32 |
| 1500 | 6.18 | 28.30 | 26.44 |
| 1700 | 6.18 | 28.30 | 26.44 |
| 2000 | 6.23 | 29.42 | 25.66 |

REV. X1
NM-BF-6
061113
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

