

Coaxial Low Pass Filter

NLP-1750+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.01	54.57	10.0	0.670
83.2	0.03	44.01	83.2	0.630
156.3	0.04	41.59	156.3	0.620
302.6	0.07	42.96	302.6	0.630
448.9	0.09	46.71	448.9	0.640
522.1	0.10	39.86	522.1	0.640
668.4	0.11	31.98	668.4	0.650
814.7	0.14	27.73	814.7	0.670
961.1	0.17	24.86	961.1	0.700
1034.2	0.17	23.60	1034.2	0.730
1107.4	0.19	22.24	1107.4	0.750
1253.7	0.25	18.78	1253.7	0.810
1326.8	0.31	16.60	1326.8	0.840
1400.0	0.42	14.05	1400.0	0.880
1650.0	2.45	4.55	1650.0	1.090
2300.0	25.15	0.18	2300.0	0.520
2600.0	34.79	0.13	2600.0	0.420
2900.0	43.62	0.12	2900.0	0.390
4450.0	74.07	0.14	4450.0	0.330
6000.0	67.71	0.12	6000.0	0.350

REV. X1
NLP-1750+
070530
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

