

Plug-In Low Pass Filter

PLP-600-75+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.00	0.03	39.03	10.00	1.680
88.80	0.06	20.33	11.91	1.580
167.50	0.17	15.95	14.07	1.730
246.30	0.23	14.87	16.62	1.770
325.00	0.24	17.52	19.64	1.660
403.80	0.23	24.71	23.20	1.610
482.50	0.45	16.54	27.40	1.680
580.00	0.67	18.62	32.00	1.650
640.00	3.15	5.36	38.24	1.650
700.00	11.10	1.10	45.17	1.650
728.00	15.12	0.69	53.36	1.650
756.00	19.01	0.52	63.04	1.660
784.00	22.88	0.40	74.46	1.660
812.00	26.53	0.34	87.96	1.650
840.00	29.84	0.32	103.91	1.650
868.00	33.13	0.28	122.75	1.650
918.40	39.24	0.25	145.00	1.660
968.80	44.53	0.23	171.29	1.670
1019.20	50.42	0.22	202.35	1.680
1059.60	56.66	0.22	235.74	1.710
1120.00	61.58	0.22	278.48	1.770
1170.00	64.81	0.22	324.43	1.840
1273.80	71.86	0.21	383.24	1.980
1377.50	74.32	0.21	446.48	2.140
1481.30	77.46	0.21	527.43	2.480
1585.00	78.86	0.21	580.00	3.150
1688.80	76.30	0.21	640.00	3.690
1792.50	75.09	0.20	840.00	1.270
1896.30	71.89	0.20	1120.00	1.500
2000.00	71.83	0.19	1163.76	1.130

REV. X1
PLP-600-75+
060725
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

