

Plug-In Low Pass Filter

PLP-750+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.00	0.01	42.40	10.00	1.220
142.50	0.13	18.90	77.50	1.270
275.00	0.13	24.00	142.50	1.310
407.50	0.24	19.50	210.00	1.290
540.00	0.34	16.10	275.00	1.380
672.50	0.50	22.50	342.50	1.480
700.00	0.61	19.60	407.50	1.490
720.00	0.75	18.80	475.00	1.580
770.00	3.29	4.70	540.00	1.800
780.00	4.47	3.50	607.50	1.960
820.00	10.67	1.20	672.50	2.420
900.00	23.62	0.50	700.00	2.780
920.00	26.64	0.40	710.00	2.810
940.00	29.60	0.40	720.00	3.180
1000.00	38.46	0.30	730.00	3.550
1040.00	44.45	0.30	770.00	3.810
1080.00	50.55	0.20	780.00	3.790
1100.00	54.84	0.20	800.00	2.990
1120.00	57.93	0.20	820.00	2.720
1150.00	64.79	0.30	870.00	1.690
1200.00	68.75	0.10	900.00	1.270
1300.00	69.77	0.10	920.00	1.110
1535.00	66.70	0.10	940.00	1.190
1602.50	70.91	0.20	1000.00	1.450
1667.00	67.12	0.10	1040.00	0.380
1735.00	66.47	0.10	1060.00	0.240
1800.00	67.59	0.10	1080.00	1.050
1867.00	66.42	0.10	1100.00	1.040
1932.00	65.70	0.10	1120.00	1.540
2000.00	67.17	0.10	1150.00	0.790

REV. X1
PLP-750+
060725
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

