

Coaxial Low Pass Filter

NLP-200+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.05	39.91	10.0	3.770
20.0	0.06	36.77	20.0	4.040
30.0	0.08	36.66	30.0	4.050
40.0	0.09	39.53	40.0	4.080
50.0	0.11	40.05	50.0	4.110
60.0	0.12	32.16	60.0	4.160
70.0	0.14	26.63	70.0	4.210
80.0	0.17	22.86	80.0	4.260
90.0	0.21	20.22	90.0	4.320
100.0	0.25	18.43	100.0	4.370
110.0	0.28	17.38	110.0	4.460
120.0	0.30	17.05	120.0	4.560
130.0	0.30	17.56	130.0	4.720
140.0	0.29	19.24	140.0	4.900
150.0	0.28	22.95	150.0	5.140
160.0	0.28	30.78	160.0	5.420
170.0	0.32	26.56	170.0	5.720
180.0	0.38	21.34	180.0	6.060
190.0	0.43	20.90	190.0	6.590
200.0	0.46	32.56	200.0	7.600
210.0	0.70	15.63	210.0	9.300
220.0	1.93	6.56	220.0	10.510
230.0	4.89	2.63	230.0	9.110
240.0	8.93	1.18	240.0	6.620
250.0	13.10	0.67	250.0	4.800
260.0	17.04	0.48	260.0	3.670
300.0	30.21	0.30	300.0	1.850
310.0	33.01	0.28	310.0	1.580
320.0	35.66	0.27	320.0	1.500
330.0	38.20	0.26	330.0	1.570
340.0	40.61	0.25	340.0	1.220
500.0	70.68	0.17	500.0	3.680
2000.0	73.72	0.17	2000.0	0.700
2500.0	56.23	0.09	2500.0	0.260
3000.0	29.70	0.15	3000.0	1.280

REV. X1
NLP-200+
080710
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

