

# Coaxial Low Pass Filter

# NLP-2950+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.01	52.68	10.0	0.490
151.6	0.04	32.88	151.6	0.470
293.2	0.07	28.39	293.2	0.470
434.7	0.09	26.51	434.7	0.470
576.3	0.10	25.60	576.3	0.470
859.5	0.12	27.73	859.5	0.480
1142.6	0.14	36.13	1142.6	0.490
1425.8	0.19	26.10	1425.8	0.510
1708.9	0.21	23.87	1708.9	0.520
1992.1	0.23	30.78	1992.1	0.560
2275.3	0.30	22.41	2275.3	0.610
2558.4	0.41	19.38	2558.4	0.710
2700.0	0.58	16.56	2700.0	0.780
2950.0	3.40	3.51	2950.0	0.970
3325.0	15.26	0.29	3325.0	0.530
3700.0	26.05	0.14	3700.0	0.380
4100.0	35.49	0.03	4100.0	0.360
4500.0	43.92	0.07	4500.0	0.250
5250.0	56.88	0.10	5250.0	0.230
6000.0	65.29	0.03	6000.0	0.250

REV. X1  
NLP-2950+  
080710  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

