

# Coaxial Low Pass Filter

# NLP-600+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.15	37.91	10.0	1.700
50.0	0.10	28.09	50.0	1.500
100.0	0.14	22.89	100.0	1.510
200.0	0.21	20.84	200.0	1.550
300.0	0.29	19.27	300.0	1.620
400.0	0.36	18.30	400.0	1.780
450.0	0.36	20.78	450.0	1.920
500.0	0.39	27.60	500.0	2.110
550.0	0.45	43.31	550.0	2.410
600.0	0.72	16.49	600.0	3.040
640.0	2.09	6.68	640.0	3.550
700.0	8.63	1.44	700.0	2.470
750.0	15.42	0.61	750.0	1.620
800.0	21.66	0.40	800.0	1.180
850.0	27.21	0.31	850.0	0.960
900.0	32.27	0.28	900.0	0.800
950.0	36.86	0.24	950.0	0.650
1000.0	41.08	0.25	1000.0	0.590
1500.0	67.58	0.25	1500.0	0.370
2000.0	69.00	0.34	2000.0	0.290
2500.0	66.77	0.36	2500.0	0.220
3000.0	65.18	0.39	3000.0	0.230

REV. X1  
NLP-600+  
060925  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

