

Coaxial Low Pass Filter

NLP-850+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.12	33.96	10.0	0.810
100.0	0.13	23.01	100.0	1.160
200.0	0.20	20.50	200.0	1.170
300.0	0.22	24.85	300.0	1.210
400.0	0.25	30.95	400.0	1.280
500.0	0.34	20.45	500.0	1.350
600.0	0.42	19.56	600.0	1.480
700.0	0.53	18.48	700.0	1.690
800.0	0.64	28.06	800.0	2.230
900.0	4.11	3.68	900.0	2.730
1000.0	14.94	0.65	1000.0	1.190
1100.0	24.71	0.37	1100.0	0.830
1150.0	28.96	0.31	1150.0	0.710
1200.0	32.87	0.29	1200.0	0.630
1250.0	36.52	0.29	1250.0	0.570
1300.0	39.91	0.26	1300.0	0.520
1400.0	46.08	0.26	1400.0	0.460
1500.0	51.50	0.27	1500.0	0.420
2000.0	70.11	0.32	2000.0	0.310
2500.0	75.80	0.34	2500.0	0.190
3000.0	78.70	0.37	3000.0	0.360

REV. X1
NLP-850+
070717
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

