

# Type-N/BNC Adaptenuator

# NM-BM-3

## Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	BNC-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
1	3.00	46.06	46.06
5	3.01	46.06	46.06
10	3.01	46.06	46.06
50	3.01	46.06	46.06
100	3.02	46.06	40.09
500	3.10	32.26	30.71
1000	3.17	25.66	28.30
1500	3.21	24.94	23.69
1700	3.23	26.44	25.66
2000	3.28	30.71	30.71

REV. X1  
NM-BM-3  
061113  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

