

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	E-Z Lock SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
10.0	0.04	41.0	40.1
50.0	0.10	36.6	36.7
100.0	0.14	48.6	47.0
200.0	0.20	44.5	41.7
300.0	0.24	41.4	39.7
400.0	0.28	43.4	40.3
500.0	0.31	49.0	44.6
600.0	0.34	40.2	41.4
700.0	0.37	35.9	36.9
800.0	0.40	31.9	32.1
900.0	0.43	28.9	28.9
1000.0	0.45	27.5	27.2
1100.0	0.48	26.9	26.2
1250.0	0.50	33.6	37.1
1500.0	0.56	29.8	28.1
1750.0	0.61	24.4	24.2
2000.0	0.64	28.8	30.3
2250.0	0.68	30.1	32.2
2500.0	0.73	25.6	25.2
2750.0	0.76	28.0	29.2
3000.0	0.79	30.6	35.0
3250.0	0.83	28.7	28.2
3500.0	0.86	34.1	32.6
3750.0	0.88	31.7	37.0
4000.0	0.90	29.7	30.1
4500.0	0.99	29.6	35.2
5000.0	1.06	33.7	39.8
5500.0	1.12	34.9	32.2
6000.0	1.19	25.9	27.8
6500.0	1.23	31.4	38.5
7000.0	1.28	34.6	33.7
7500.0	1.35	28.2	33.1
8000.0	1.55	21.8	24.4
8500.0	1.52	31.6	26.7
9000.0	1.55	21.2	22.2
9500.0	1.46	26.2	23.6
10000.0	1.54	24.0	20.9
10500.0	1.66	21.3	21.0
11000.0	1.71	30.1	23.5
11500.0	1.86	22.1	22.9
12000.0	2.04	19.7	19.3
12500.0	2.12	23.7	16.8
13000.0	1.96	32.6	25.5
13500.0	1.84	22.2	21.9
14000.0	1.91	26.1	19.6
14500.0	1.96	34.3	29.6
15000.0	1.90	23.0	23.2
15500.0	1.98	21.1	25.7
16000.0	2.08	23.9	32.5
16500.0	2.02	36.2	30.1
17000.0	2.14	25.6	27.5
17500.0	2.27	33.7	35.7
18000.0	2.15	22.5	23.7