

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	E-Z Lock SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
10.0	0.04	42.2	42.2
50.0	0.09	38.2	37.4
100.0	0.12	53.8	52.9
200.0	0.18	46.8	57.6
300.0	0.21	43.3	41.7
400.0	0.25	37.8	37.3
500.0	0.28	33.0	32.6
600.0	0.31	30.5	30.1
700.0	0.34	30.3	29.9
800.0	0.36	36.6	34.4
900.0	0.40	43.3	37.6
1000.0	0.41	31.3	29.9
1100.0	0.43	27.8	26.9
1250.0	0.45	33.8	32.8
1500.0	0.50	37.2	33.9
1750.0	0.55	33.9	30.3
2000.0	0.59	29.1	27.5
2250.0	0.64	26.1	25.7
2500.0	0.68	25.6	25.4
2750.0	0.71	26.7	26.4
3000.0	0.74	28.7	28.2
3250.0	0.77	33.8	30.8
3500.0	0.80	34.7	30.0
3750.0	0.83	31.2	28.0
4000.0	0.87	29.4	28.1
4500.0	0.94	28.4	31.4
5000.0	1.00	35.7	37.6
5500.0	1.05	28.1	28.9
6000.0	1.12	31.9	29.5
6500.0	1.19	26.7	29.5
7000.0	1.22	28.2	28.7
7500.0	1.28	29.1	29.2
8000.0	1.29	26.9	28.3
8500.0	1.34	25.0	28.3
9000.0	1.35	24.3	25.3
9500.0	1.42	21.8	22.8
10000.0	1.48	22.7	25.6
10500.0	1.51	27.6	29.8
11000.0	1.67	18.6	21.3
11500.0	1.67	19.0	20.8
12000.0	1.66	25.8	34.1
12500.0	1.72	21.3	23.7
13000.0	1.75	19.0	20.2
13500.0	1.77	23.3	25.0
14000.0	1.74	24.4	29.6
14500.0	1.90	20.6	21.0
15000.0	1.89	26.6	24.0
15500.0	1.87	32.7	32.4
16000.0	1.99	25.3	25.5
16500.0	1.99	33.2	33.4
17000.0	2.05	30.4	32.5
17500.0	2.09	26.1	35.2
18000.0	2.14	26.7	25.4