

Plug-In Low Pass Filter

PLP-200+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.00	0.08	28.60	10.00	4.180
37.50	0.12	30.10	37.50	4.310
67.50	0.15	32.80	67.50	4.380
95.00	0.26	18.50	95.00	4.780
122.50	0.43	14.30	122.50	5.090
150.00	0.39	17.40	150.00	5.750
190.00	0.58	21.00	190.00	8.300
200.00	0.96	13.60	195.00	9.070
210.00	2.52	5.90	200.00	10.180
220.00	6.01	2.40	205.00	11.130
240.00	15.07	0.70	210.00	11.420
250.00	19.34	0.60	220.00	9.610
260.00	23.25	0.50	235.00	5.780
280.00	30.20	0.40	240.00	5.000
290.00	33.33	0.40	245.00	4.340
300.00	36.17	0.30	250.00	3.630
320.00	41.60	0.30	260.00	2.950
370.00	53.41	0.20	280.00	1.790
380.00	55.00	0.20	290.00	1.540
385.00	56.23	0.20	300.00	1.210
390.00	57.87	0.20	310.00	0.880
490.00	71.86	0.10	320.00	0.150
550.00	72.71	0.10	340.00	1.770
602.50	74.42	0.10	370.00	0.310
660.00	77.14	0.00	380.00	2.760
715.00	72.38	0.10	385.00	1.860
750.00	73.49	0.10	390.00	1.940
780.00	73.91	0.10	490.00	1.920
790.00	80.33	0.10	517.50	1.910
800.00	77.51	0.10	550.00	1.810

REV. X1
PLP-200+
060725
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

