

Plug-In Low Pass Filter

PLP-600+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.00	0.01	39.30	10.00	1.410
152.50	0.22	16.20	80.00	1.440
295.00	0.20	25.30	152.50	1.380
437.50	0.28	20.50	222.50	1.420
507.50	0.37	21.90	295.00	1.590
577.50	0.59	22.00	365.00	1.790
580.00	0.60	21.90	437.50	1.950
620.00	1.50	9.60	507.50	2.270
640.00	2.98	5.10	577.50	2.860
670.00	7.09	2.10	580.00	2.850
720.00	15.52	0.40	600.00	3.360
800.00	28.44	0.30	620.00	3.840
820.00	31.52	0.30	630.00	3.980
830.00	33.06	0.30	640.00	3.810
840.00	34.63	0.30	670.00	3.370
880.00	41.22	0.20	700.00	2.260
920.00	48.84	0.20	720.00	2.300
960.00	58.62	0.20	750.00	1.480
1000.00	59.95	0.20	800.00	0.770
1100.00	59.89	0.10	820.00	0.930
1120.00	62.05	0.10	830.00	1.540
1360.00	71.05	0.10	840.00	1.000
1502.50	73.53	0.20	880.00	0.790
1572.50	70.71	0.10	900.00	1.010
1650.00	67.12	0.10	920.00	1.110
1750.00	67.73	0.10	940.00	1.280
1800.00	70.74	0.10	960.00	1.150
1850.00	68.64	0.10	1000.00	1.020
1950.00	68.21	0.10	1100.00	0.950
2000.00	65.82	0.10	1120.00	0.850

REV. X1
PLP-600+
060725
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

