

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	E-Z Lock SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
10.0	0.02	44.8	44.2
50.0	0.06	37.0	37.8
100.0	0.08	39.7	39.0
200.0	0.12	37.1	36.9
400.0	0.17	33.7	33.2
500.0	0.19	36.2	34.8
600.0	0.21	30.8	30.5
700.0	0.22	32.6	31.1
800.0	0.24	33.4	33.4
900.0	0.26	28.3	27.2
1000.0	0.26	37.6	40.3
1100.0	0.29	26.3	25.4
1250.0	0.31	28.0	26.4
1500.0	0.34	26.0	26.0
1750.0	0.36	34.6	36.2
2000.0	0.40	25.0	24.9
2250.0	0.41	28.8	30.1
2500.0	0.44	29.3	30.2
2750.0	0.47	26.3	26.0
3000.0	0.48	31.5	35.7
3250.0	0.51	28.7	27.7
3500.0	0.52	33.3	33.1
3750.0	0.53	29.3	30.1
4000.0	0.54	32.0	32.3
4500.0	0.59	32.1	31.6
5000.0	0.65	29.1	29.5
5500.0	0.70	26.2	27.0
6000.0	0.74	26.0	28.3
6500.0	0.76	30.8	34.6
7000.0	0.80	27.4	28.4
7500.0	0.83	25.4	25.5
8000.0	0.88	25.5	25.1
8500.0	0.92	22.6	24.8
9000.0	0.96	20.5	21.0
9500.0	0.88	25.1	23.2
10000.0	0.93	23.0	20.3
10500.0	1.02	18.6	19.0
11000.0	1.06	17.9	19.9
11500.0	1.20	17.9	17.7
12000.0	1.28	19.1	17.0
12500.0	1.28	24.0	18.0
13000.0	1.24	28.5	24.8
13500.0	1.15	24.1	22.2
14000.0	1.17	22.8	26.3
14500.0	1.24	23.7	23.4
15000.0	1.17	21.2	26.6
15500.0	1.17	21.9	43.3
16000.0	1.23	27.0	36.8
16500.0	1.17	27.1	27.8
17000.0	1.32	20.6	21.2
17500.0	1.44	18.7	19.3
18000.0	1.38	17.2	16.2