

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	E-Z Lock SMA-MALE RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
10.0	0.06	40.6	40.7
50.0	0.12	37.2	37.2
100.0	0.16	42.6	42.5
200.0	0.23	39.1	39.4
300.0	0.29	38.8	40.1
400.0	0.33	47.1	47.0
500.0	0.37	41.6	41.5
600.0	0.41	34.4	34.7
700.0	0.45	31.1	31.3
800.0	0.48	30.7	30.7
900.0	0.51	30.3	30.4
1000.0	0.54	34.8	35.0
1100.0	0.56	41.4	44.5
1250.0	0.61	29.8	29.8
1500.0	0.67	27.4	27.6
1750.0	0.73	28.7	28.9
2000.0	0.78	31.9	31.9
2250.0	0.83	36.4	34.8
2500.0	0.88	39.9	51.5
2750.0	0.92	33.2	36.0
3000.0	0.97	31.0	32.2
3250.0	1.01	29.9	30.5
3500.0	1.05	29.8	30.0
3750.0	1.09	30.3	29.8
4000.0	1.13	29.3	29.3
4250.0	1.17	33.5	33.7
4500.0	1.21	36.4	41.5
5000.0	1.28	31.2	30.8
5500.0	1.35	36.7	33.6
6000.0	1.43	40.7	32.8
6500.0	1.49	40.7	30.9
7000.0	1.54	44.8	31.9
7500.0	1.63	41.5	36.0
8000.0	1.68	31.1	32.4
8500.0	1.76	27.5	25.7
9000.0	1.81	30.6	28.4
9500.0	1.86	29.3	31.4
10000.0	1.93	26.4	30.4
10500.0	2.00	22.4	25.0
11000.0	2.07	21.7	22.4
11500.0	2.10	23.1	27.3
12000.0	2.17	22.4	27.7
13000.0	2.27	20.8	22.8
13500.0	2.30	20.4	24.2
14000.0	2.35	20.9	27.8
14500.0	2.38	20.8	23.0
15000.0	2.43	21.3	23.0
15500.0	2.48	24.5	26.6
16000.0	2.56	25.4	31.1
16500.0	2.60	22.7	24.7
17000.0	2.66	26.5	27.0
17500.0	2.70	32.2	30.2
18000.0	2.74	23.7	25.0