


Voltage Variable Attenuator


RVA-2500+

Typical Performance Curves


Attenuation @ 1000 MHz




Attenuation @ V+=3 V




Attenuation @ V+=5 V




Input Return Loss @ V+=3 V




Input Return Loss @ V+=5 V



Output Return Loss @ V+=3 V



Output Return Loss @ V+=5 V



REV. X1
RVA-2500+
070320
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Voltage Variable Attenuator


RVA-2500+

Typical Performance Curves


Input IP3 @ V+=3 V




Input IP3 @ V+=5 V



Phase Shift @ V+=3 V



Phase Shift @ V+=5 V



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



REV. X1
RVA-2500+
070320
Page 2 of 2