

Surface Mount Low Pass Filter

SALF-146

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
1	0.03	0.03	0.06	49.25	48.92	43.45	49.65	49.09	43.49
10	0.06	0.06	0.09	37.38	38.46	37.65	36.91	37.45	37.29
20	0.08	0.08	0.11	32.53	33.53	33.49	31.60	32.07	32.52
30	0.10	0.10	0.14	31.37	32.36	32.20	29.69	29.98	30.32
40	0.11	0.12	0.16	33.20	34.09	33.51	29.45	29.41	29.43
50	0.13	0.14	0.18	35.06	35.33	35.83	28.77	28.53	28.44
60	0.15	0.17	0.21	28.17	28.57	30.00	25.44	25.54	25.78
70	0.19	0.21	0.25	22.39	22.88	23.90	21.39	21.76	22.24
80	0.24	0.26	0.30	18.62	19.12	19.83	18.17	18.62	19.12
90	0.30	0.32	0.36	16.17	16.62	17.12	15.95	16.36	16.83
100	0.36	0.39	0.43	14.79	15.16	15.49	14.68	15.02	15.42
130	0.40	0.47	0.54	17.93	17.72	17.38	18.01	17.68	17.71
146	0.45	0.54	0.64	25.60	24.17	22.46	26.55	24.77	23.77
160	0.82	0.96	1.11	14.98	14.51	13.87	15.19	14.75	14.22
172	3.51	3.76	4.00	4.26	4.29	4.27	4.21	4.25	4.21
198	20.68	20.94	21.20	0.35	0.42	0.46	0.33	0.39	0.45
200	22.02	22.29	22.55	0.32	0.38	0.42	0.30	0.36	0.42
210	28.52	28.81	29.11	0.22	0.28	0.31	0.22	0.26	0.33
229	40.16	40.51	40.84	0.15	0.20	0.22	0.16	0.19	0.27
240	46.42	46.78	47.12	0.14	0.18	0.20	0.15	0.18	0.25
275	57.27	57.51	57.67	0.12	0.15	0.16	0.14	0.15	0.24
300	56.11	56.32	56.25	0.11	0.14	0.16	0.14	0.14	0.24
350	53.05	53.15	53.21	0.11	0.13	0.14	0.14	0.14	0.25
400	51.54	51.62	51.71	0.11	0.13	0.15	0.14	0.14	0.26
450	50.86	50.84	50.90	0.11	0.13	0.15	0.15	0.15	0.27
500	50.50	50.53	50.57	0.10	0.13	0.14	0.15	0.15	0.28
600	51.02	51.14	51.17	0.10	0.13	0.15	0.15	0.15	0.29
650	52.57	52.71	52.76	0.11	0.13	0.15	0.16	0.16	0.30
700	55.55	55.81	55.98	0.10	0.13	0.15	0.16	0.16	0.30
750	66.82	68.44	69.72	0.10	0.13	0.16	0.17	0.17	0.31
800	58.44	57.77	57.18	0.11	0.14	0.17	0.17	0.17	0.31
850	47.62	47.40	47.09	0.10	0.14	0.16	0.17	0.18	0.32
900	40.47	40.34	40.03	0.11	0.15	0.18	0.18	0.19	0.33
1000	26.26	26.04	25.54	0.18	0.23	0.28	0.27	0.31	0.48
1100	24.77	25.17	25.53	0.19	0.24	0.28	0.31	0.33	0.49
1200	37.70	38.04	38.35	0.13	0.19	0.25	0.27	0.33	0.49
1300	32.44	32.29	31.98	0.15	0.22	0.29	0.56	0.67	0.86
1400	15.92	16.06	16.11	0.31	0.40	0.49	6.43	7.19	7.82
1500	21.50	21.72	21.98	0.22	0.32	0.43	0.69	0.74	0.94
1600	25.73	25.90	26.15	0.23	0.33	0.46	0.35	0.41	0.62
1700	29.07	29.31	29.87	0.26	0.38	0.53	0.31	0.39	0.61
1800	35.00	35.45	36.10	0.28	0.42	0.58	0.31	0.41	0.63
1900	47.49	45.10	43.26	0.33	0.47	0.66	0.31	0.43	0.67
2000	29.38	28.70	28.19	0.38	0.54	0.75	0.34	0.47	0.73
2100	21.77	21.21	20.82	0.47	0.66	0.90	0.38	0.54	0.83
2200	15.87	15.31	14.91	0.69	0.94	1.25	0.52	0.73	1.06
2300	10.38	9.80	9.41	1.32	1.78	2.32	0.88	1.20	1.64
2400	5.56	5.19	5.08	3.35	4.55	5.95	1.99	2.57	3.23
2500	3.22	3.44	3.88	6.36	7.50	8.53	3.51	3.83	4.12
2600	3.78	4.25	4.88	4.48	4.82	5.22	2.93	2.99	3.14
2700	4.96	5.37	6.02	2.85	3.27	3.79	2.06	2.21	2.43
2800	5.92	6.30	7.11	2.21	2.82	3.71	1.61	1.81	2.08
2900	6.38	7.18	9.06	2.11	3.63	6.34	1.40	1.64	1.95
3000	7.69	10.22	7.68	4.46	8.62	5.16	1.31	1.56	2.03

REV. X2
SALF-146
101021
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Low Pass Filter

SALF-146

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
0.1	4.38	4.32	4.41
0.2	4.35	4.34	4.39
0.3	4.32	4.34	4.35
0.4	4.29	4.30	4.33
0.5	4.30	4.31	4.33
0.6	4.29	4.30	4.32
0.7	4.28	4.29	4.30
0.8	4.28	4.29	4.30
0.9	4.27	4.28	4.29
1.0	4.26	4.27	4.28
10.0	4.19	4.21	4.21
20.0	4.20	4.21	4.22
30.0	4.24	4.25	4.26
40.0	4.32	4.32	4.33
50.0	4.42	4.43	4.43
60.0	4.55	4.56	4.56
70.0	4.70	4.71	4.72
80.0	4.87	4.88	4.90
90.0	5.07	5.08	5.10
100.0	5.33	5.35	5.37
110.0	5.68	5.70	5.72
120.0	6.20	6.21	6.23
130.0	6.92	6.94	6.96
140.0	7.93	7.96	7.99
146.0	8.75	8.79	8.84
150.0	9.47	9.53	9.58
160.0	12.36	12.40	12.44
170.0	15.00	14.88	14.78
172.0	14.82	14.68	14.57
180.0	11.62	11.51	11.45
190.0	7.29	7.25	7.26
198.0	5.30	5.28	5.28
200.0	4.95	4.93	4.93
210.0	3.73	3.70	3.69
220.0	3.00	2.98	2.95
229.0	2.58	2.57	2.57
230.0	2.58	2.53	2.53
240.0	2.41	2.35	2.37
250.0	2.33	2.29	2.35
275.0	1.63	1.58	1.82
300.0	1.10	0.92	0.97
350.0	0.57	0.52	0.52
400.0	0.36	0.45	0.55
450.0	0.43	0.33	0.39
500.0	0.30	0.23	0.22
550.0	0.18	0.19	0.21
600.0	0.26	0.15	0.32
650.0	0.25	0.14	0.05
700.0	0.17	0.30	0.20
750.0	4.62	7.04	11.42
800.0	3.35	2.56	2.07
850.0	0.12	0.10	0.10
900.0	0.38	0.13	0.45

REV. X2
SALF-146
101021
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

