

Surface Mount Low Pass Filter

SALF-265+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
1	0.02	0.02	0.05	53.97	51.39	44.47	55.24	51.38	44.42
50	0.08	0.10	0.13	29.05	29.36	29.09	29.25	29.59	30.66
60	0.09	0.11	0.14	28.50	28.51	27.95	28.77	28.77	29.56
70	0.10	0.12	0.16	28.48	28.10	27.23	28.82	28.40	28.83
80	0.11	0.13	0.17	28.94	28.09	26.83	29.36	28.39	28.40
90	0.11	0.14	0.18	29.82	28.39	26.69	30.53	28.87	28.36
100	0.12	0.15	0.19	31.18	29.14	26.95	32.64	29.95	28.79
110	0.13	0.16	0.21	32.75	30.29	27.59	36.29	31.81	29.78
120	0.14	0.17	0.22	33.64	31.68	28.66	42.09	34.80	31.47
130	0.15	0.18	0.23	33.00	32.67	30.17	40.41	38.91	34.02
140	0.16	0.19	0.24	31.21	32.46	31.89	34.64	38.67	36.37
150	0.17	0.21	0.25	29.46	31.01	32.78	31.11	34.24	35.48
160	0.18	0.22	0.27	28.10	29.29	31.90	28.97	30.91	32.35
170	0.19	0.24	0.29	27.25	27.93	30.14	27.74	28.80	29.75
180	0.21	0.26	0.30	26.99	27.11	28.60	27.16	27.55	27.98
190	0.22	0.28	0.33	27.34	26.88	27.62	27.14	26.97	26.91
200	0.23	0.29	0.35	28.45	27.35	27.34	27.68	27.05	26.52
210	0.25	0.31	0.37	30.73	28.81	27.93	28.85	27.91	26.90
220	0.26	0.33	0.39	34.76	31.88	29.64	30.37	29.72	28.23
230	0.28	0.35	0.41	38.49	39.29	33.48	31.33	32.52	31.12
240	0.31	0.38	0.44	33.19	41.01	39.99	30.19	33.82	36.30
250	0.33	0.41	0.48	28.49	30.88	32.94	27.79	30.30	34.27
265	0.40	0.49	0.57	24.02	24.25	24.53	23.88	24.23	24.78
280	0.52	0.64	0.74	18.96	18.74	18.43	18.33	18.06	17.74
290	0.74	0.88	1.00	14.33	14.22	14.00	13.59	13.40	13.11
308	2.14	2.37	2.55	6.54	6.56	6.55	6.01	5.96	5.86
320	4.46	4.78	5.01	3.29	3.35	3.39	2.90	2.91	2.88
330	7.23	7.61	7.89	1.82	1.91	1.96	1.52	1.57	1.57
340	10.43	10.86	11.18	1.06	1.17	1.22	0.83	0.90	0.92
350	13.81	14.26	14.62	0.69	0.80	0.84	0.51	0.58	0.62
360	17.23	17.70	18.08	0.50	0.60	0.64	0.35	0.43	0.47
370	20.62	21.09	21.50	0.39	0.49	0.52	0.27	0.35	0.39
380	23.93	24.39	24.82	0.33	0.42	0.45	0.23	0.30	0.35
390	27.14	27.59	28.03	0.29	0.38	0.41	0.21	0.27	0.33
400	30.23	30.67	31.12	0.26	0.35	0.37	0.19	0.26	0.32
410	33.18	33.61	34.05	0.24	0.32	0.34	0.18	0.24	0.31
420	35.99	36.41	36.85	0.22	0.29	0.32	0.17	0.23	0.30
430	38.66	39.06	39.49	0.20	0.27	0.30	0.16	0.22	0.29
440	41.19	41.55	41.97	0.19	0.26	0.28	0.16	0.22	0.29
470	47.27	47.64	47.86	0.17	0.23	0.25	0.15	0.21	0.30
490	49.65	49.96	50.10	0.16	0.23	0.24	0.16	0.21	0.30
550	50.33	50.69	50.46	0.14	0.20	0.22	0.15	0.20	0.31
625	48.44	48.85	48.52	0.13	0.18	0.20	0.16	0.20	0.32
825	46.85	47.30	46.99	0.12	0.16	0.18	0.18	0.22	0.35
950	49.04	49.56	49.29	0.12	0.16	0.18	0.18	0.22	0.36
1000	51.89	52.36	52.45	0.12	0.17	0.19	0.18	0.22	0.36
1100	58.42	57.85	56.94	0.12	0.18	0.20	0.18	0.23	0.38
1200	40.98	40.64	40.46	0.12	0.19	0.23	0.19	0.25	0.40
1300	29.73	29.52	29.16	0.15	0.22	0.28	0.23	0.31	0.48
1400	12.84	12.02	11.36	0.94	1.33	1.75	1.55	2.21	3.10
1500	20.48	21.06	21.50	0.24	0.33	0.41	0.35	0.44	0.61
2000	22.09	21.62	21.23	0.33	0.51	0.67	1.90	2.36	2.95
2500	8.37	7.88	7.54	1.47	1.97	2.47	1.36	1.89	2.52
3000	4.92	5.15	5.57	2.39	2.85	3.23	2.00	2.28	2.54

REV. X2
SALF-265+
101021
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Low Pass Filter

SALF-265+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
0.1	2.13	2.13	2.20
0.2	2.09	2.09	2.21
0.3	2.19	2.19	2.24
0.4	2.21	2.21	2.23
0.5	2.21	2.21	2.25
0.6	2.21	2.22	2.24
0.7	2.21	2.22	2.24
0.8	2.21	2.22	2.24
0.9	2.22	2.22	2.24
1.0	2.22	2.23	2.24
40	2.20	2.20	2.21
50	2.21	2.21	2.22
60	2.22	2.23	2.23
70	2.25	2.25	2.25
80	2.27	2.27	2.27
90	2.30	2.30	2.31
100	2.34	2.34	2.34
110	2.37	2.37	2.38
120	2.42	2.42	2.42
130	2.47	2.47	2.47
140	2.52	2.53	2.53
150	2.58	2.59	2.60
160	2.65	2.66	2.67
170	2.72	2.73	2.74
180	2.81	2.82	2.83
190	2.91	2.91	2.93
200	3.02	3.03	3.04
210	3.16	3.16	3.17
220	3.31	3.32	3.33
230	3.48	3.50	3.51
240	3.69	3.71	3.73
250	3.94	3.96	3.99
265	4.45	4.49	4.52
280	5.26	5.30	5.34
290	6.03	6.08	6.12
308	7.31	7.33	7.35
320	7.01	6.96	6.96
330	6.07	5.98	5.96
340	5.04	4.93	4.90
350	4.15	4.05	4.00
360	3.43	3.33	3.28
370	2.86	2.78	2.72
380	2.40	2.33	2.28
390	2.05	2.00	1.95
400	1.82	1.77	1.72
410	1.67	1.64	1.59
420	1.62	1.56	1.55
430	1.60	1.54	1.53
440	1.58	1.50	1.46
470	1.32	1.22	1.17
490	1.09	1.07	1.05
550	0.66	0.61	0.63
625	0.54	0.46	0.66
900	0.14	0.75	0.32

REV. X2
SALF-265+
101021
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

