

Surface Mount Low Pass Filter

SALF-396

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
1	0.02	0.05	0.06	51.68	44.58	43.43	52.89	45.06	43.86
10	0.03	0.06	0.07	41.29	39.35	38.32	41.59	39.27	38.27
20	0.04	0.07	0.08	35.90	34.79	33.79	36.24	34.68	33.69
30	0.05	0.09	0.09	32.71	31.88	31.00	32.93	31.66	30.75
40	0.06	0.10	0.11	30.36	29.77	29.00	30.47	29.47	28.68
50	0.07	0.11	0.12	28.47	28.10	27.51	28.54	27.76	27.14
60	0.08	0.12	0.13	26.90	26.75	26.35	26.91	26.37	25.93
70	0.09	0.13	0.14	25.49	25.60	25.42	25.54	25.23	24.99
80	0.10	0.14	0.15	24.26	24.58	24.62	24.37	24.30	24.27
90	0.11	0.16	0.16	23.16	23.73	23.99	23.32	23.46	23.68
100	0.12	0.17	0.18	22.18	22.96	23.47	22.38	22.73	23.17
110	0.13	0.18	0.19	21.34	22.31	23.05	21.52	22.07	22.73
120	0.15	0.19	0.20	20.61	21.74	22.70	20.75	21.47	22.34
130	0.16	0.20	0.21	19.98	21.26	22.40	20.05	20.91	21.96
140	0.16	0.21	0.21	19.42	20.80	22.12	19.44	20.42	21.62
150	0.18	0.22	0.22	18.98	20.43	21.90	18.93	19.99	21.30
200	0.23	0.28	0.28	17.95	19.36	20.86	18.00	19.03	20.43
300	0.26	0.36	0.39	24.10	23.64	22.93	24.25	23.56	22.89
320	0.27	0.37	0.41	27.80	26.69	25.07	28.14	26.94	25.30
396	0.41	0.55	0.62	35.26	34.48	32.24	37.26	36.82	35.85
400	0.42	0.57	0.63	35.25	34.22	31.44	36.26	36.01	33.84
420	0.53	0.70	0.78	23.78	23.21	22.24	23.42	23.42	22.48
458	1.75	2.08	2.26	8.00	7.74	7.63	7.99	7.83	7.71
500	8.50	9.10	9.46	1.47	1.55	1.59	1.48	1.58	1.61
505	9.72	10.33	10.70	1.22	1.31	1.36	1.23	1.34	1.38
540	18.97	19.57	20.00	0.48	0.61	0.66	0.49	0.62	0.67
565	26.10	26.70	27.18	0.35	0.47	0.52	0.34	0.47	0.52
600	38.67	39.37	39.96	0.28	0.39	0.44	0.27	0.40	0.44
620	50.62	52.00	52.68	0.26	0.37	0.41	0.25	0.38	0.42
700	47.15	47.49	47.93	0.20	0.30	0.34	0.21	0.34	0.38
800	65.34	67.74	70.28	0.17	0.25	0.29	0.20	0.33	0.37
900	50.40	50.04	49.84	0.16	0.23	0.26	0.20	0.33	0.37
1000	45.89	45.73	45.63	0.15	0.21	0.24	0.20	0.34	0.38
1100	43.97	43.98	43.83	0.14	0.20	0.23	0.20	0.34	0.38
1200	43.05	43.10	42.96	0.13	0.19	0.22	0.19	0.34	0.39
1300	45.49	45.63	45.41	0.13	0.18	0.22	0.19	0.35	0.40
1400	59.18	60.35	60.66	0.12	0.18	0.22	0.19	0.36	0.42
1430	51.40	50.70	50.18	0.12	0.18	0.23	0.19	0.36	0.42
1500	34.77	34.47	34.12	0.14	0.21	0.27	0.24	0.42	0.49
1600	15.17	14.44	13.60	0.63	0.85	1.11	1.28	1.86	2.43
1700	17.66	18.23	18.65	0.28	0.36	0.42	0.44	0.63	0.69
1800	21.39	21.72	21.90	0.20	0.29	0.38	0.30	0.50	0.59
1900	22.17	22.39	22.50	0.22	0.33	0.44	0.29	0.50	0.61
2000	22.48	22.68	22.75	0.24	0.36	0.49	0.29	0.52	0.65
2100	22.44	22.61	22.67	0.26	0.39	0.54	0.31	0.55	0.70
2200	22.68	22.87	22.90	0.30	0.44	0.61	0.34	0.59	0.75
2300	22.92	23.14	23.19	0.31	0.46	0.65	0.36	0.62	0.81
2400	23.52	23.74	23.77	0.32	0.48	0.69	0.37	0.63	0.84
2500	24.85	25.04	25.10	0.31	0.48	0.70	0.38	0.65	0.87
2600	28.82	28.96	29.02	0.31	0.49	0.72	0.39	0.66	0.89
2700	45.93	47.43	46.44	0.37	0.55	0.77	0.41	0.67	0.91
2800	20.43	20.89	20.99	0.43	0.63	0.87	0.55	0.83	1.10
2900	9.94	9.87	9.77	1.02	1.34	1.68	1.48	1.91	2.34
3000	2.72	3.00	3.30	6.46	6.93	7.13	13.26	16.74	19.43

REV. X2
SALF-396
101024
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Low Pass Filter

SALF-396

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
1	1.21	1.21	1.21
10	1.22	1.22	1.22
20	1.20	1.21	1.21
30	1.20	1.21	1.21
40	1.20	1.21	1.20
50	1.20	1.21	1.20
60	1.21	1.21	1.21
70	1.21	1.21	1.21
80	1.22	1.22	1.21
90	1.22	1.22	1.22
100	1.23	1.23	1.23
110	1.23	1.24	1.24
120	1.24	1.25	1.25
130	1.25	1.26	1.26
140	1.27	1.27	1.28
150	1.28	1.29	1.29
160	1.30	1.30	1.31
170	1.31	1.32	1.32
180	1.32	1.33	1.34
200	1.36	1.36	1.37
210	1.38	1.39	1.40
220	1.41	1.42	1.43
230	1.45	1.45	1.46
240	1.48	1.48	1.49
250	1.51	1.52	1.52
260	1.55	1.55	1.55
270	1.58	1.59	1.59
280	1.62	1.63	1.63
290	1.67	1.67	1.68
300	1.73	1.73	1.73
310	1.79	1.79	1.79
320	1.85	1.85	1.86
330	1.91	1.92	1.93
340	1.98	2.00	2.00
350	2.06	2.08	2.09
396	2.64	2.66	2.68
400	2.71	2.74	2.76
450	4.35	4.39	4.42
458	4.61	4.63	4.65
460	4.67	4.68	4.69
470	4.83	4.78	4.78
480	4.76	4.66	4.63
490	4.43	4.29	4.25
500	3.90	3.77	3.71
505	3.61	3.48	3.42
540	2.13	2.07	2.03
565	1.70	1.64	1.60
600	0.74	0.74	0.65
650	3.21	2.45	0.68
700	0.30	0.14	0.21
750	0.48	0.44	0.35
800	6.85	12.05	15.73
850	0.11	0.03	0.23
900	0.01	0.31	0.80

REV. X2
SALF-396
101024
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

