

# Surface Mount High Pass Filter

# RHP-EDU2190

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	108.86	0.05	1000	1.19
50	99.86	0.04	1025	1.08
100	93.52	0.04	1050	0.98
250	69.75	0.07	1100	0.83
380	49.80	0.15	1120	0.79
500	38.21	0.28	1150	0.73
710	32.45	0.54	1180	0.69
715	30.21	0.55	1200	0.65
730	24.87	0.60	1220	0.62
745	20.62	0.66	1240	0.60
780	12.75	1.00	1260	0.57
848	3.09	4.74	1280	0.55
850	2.94	4.97	1300	0.53
900	0.93	12.84	1350	0.49
1000	0.47	33.65	1400	0.45
1500	0.36	19.20	1450	0.42
1600	0.34	19.42	1500	0.39
1800	0.33	19.87	1550	0.37
2000	0.31	20.63	1600	0.35
2200	0.31	21.66	1650	0.33
2400	0.32	21.88	1700	0.31
2600	0.34	20.50	1750	0.30
2800	0.37	18.23	1775	0.29
3000	0.42	15.89	1800	0.28