

Coaxial High Pass Filter

SHP-100A+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	72.11	0.05	84.0	22.02
50.0	57.35	1.13	88.0	31.80
75.0	58.56	1.33	90.0	37.99
77.0	46.88	1.38	100.0	27.06
80.0	34.21	1.48	120.0	10.61
82.0	27.39	1.60	130.0	7.80
83.0	24.28	1.68	140.0	6.12
88.0	10.95	2.87	150.0	4.99
90.0	6.93	4.36	160.0	4.17
92.0	4.13	7.12	170.0	3.55
94.0	2.55	11.26	180.0	3.08
100.0	1.18	29.89	190.0	2.72
110.0	0.71	40.57	200.0	2.42
150.0	0.35	21.43	250.0	1.54
200.0	0.37	14.40	300.0	1.13
300.0	0.38	12.83	350.0	0.90
400.0	0.36	12.97	400.0	0.76
500.0	0.34	13.15	450.0	0.65
600.0	0.34	13.15	500.0	0.59
650.0	0.35	13.08	600.0	0.54
700.0	0.36	13.00	700.0	0.46
800.0	0.39	12.70	800.0	0.430
1000.0	0.42	12.53	1000.0	0.380
2000.0	0.65	10.97	2000.0	0.340
3000.0	0.88	17.25	3000.0	0.340

REV. X1
SHP-100A+
070208
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

