

Typical Performance Data

| FREQUENCY (MHz) | INSERTION LOSS (dB) | RETURN LOSS (dB) |
|--------------------|---------------------------|------------------------|
| 0.30 | 2.14 | 8.01 |
| 0.40 | 1.85 | 9.39 |
| 0.50 | 1.71 | 10.27 |
| 0.60 | 1.61 | 10.87 |
| 0.70 | 1.54 | 11.30 |
| 1.00 | 1.41 | 12.17 |
| 2.00 | 1.12 | 13.69 |
| 3.00 | 1.01 | 14.41 |
| 4.00 | 0.95 | 14.78 |
| 5.00 | 0.93 | 14.98 |
| 6.00 | 0.91 | 15.12 |
| 7.00 | 0.90 | 15.19 |
| 8.00 | 0.89 | 15.23 |
| 9.00 | 0.88 | 15.24 |
| 10.00 | 0.88 | 15.22 |
| 12.00 | 0.87 | 15.15 |
| 14.00 | 0.88 | 15.03 |
| 16.00 | 0.88 | 14.87 |
| 18.00 | 0.89 | 14.68 |
| 20.00 | 0.90 | 14.49 |
| 26.00 | 0.93 | 13.81 |
| 32.00 | 0.98 | 13.08 |
| 38.00 | 1.03 | 12.35 |
| 44.00 | 1.08 | 11.64 |
| 50.00 | 1.15 | 10.97 |
| 55.00 | 1.20 | 10.44 |
| 60.00 | 1.26 | 9.95 |
| 65.00 | 1.33 | 9.47 |
| 70.00 | 1.39 | 9.03 |
| 75.00 | 1.46 | 8.63 |
| 80.00 | 1.52 | 8.23 |
| 84.00 | 1.58 | 7.93 |
| 88.00 | 1.64 | 7.64 |
| 92.00 | 1.70 | 7.38 |
| 96.00 | 1.76 | 7.12 |
| 100.00 | 1.82 | 6.88 |
| 104.00 | 1.88 | 6.65 |
| 108.00 | 1.95 | 6.44 |
| 112.00 | 2.01 | 6.22 |
| 116.00 | 2.08 | 6.02 |
| 120.00 | 2.15 | 5.82 |