

Surface Mount Low Pass Filter

SALF-490+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
1	0.03	0.07	0.05	49.04	41.52	44.86	50.77	41.90	45.47
10	0.04	0.08	0.06	40.81	38.79	41.10	40.97	39.37	41.46
20	0.04	0.09	0.07	35.22	34.90	36.52	35.21	35.51	36.77
30	0.05	0.10	0.08	31.83	31.87	33.21	31.84	32.57	33.48
40	0.06	0.11	0.09	29.41	29.58	30.69	29.50	30.33	31.04
50	0.07	0.12	0.10	27.65	27.71	28.64	27.80	28.59	29.07
60	0.08	0.13	0.11	26.28	26.23	26.96	26.49	27.18	27.42
70	0.09	0.14	0.12	25.23	25.02	25.57	25.45	25.99	26.02
80	0.09	0.15	0.14	24.43	24.04	24.38	24.58	24.94	24.76
90	0.10	0.16	0.15	23.77	23.21	23.35	23.90	24.07	23.68
100	0.11	0.18	0.16	23.26	22.51	22.46	23.36	23.34	22.75
200	0.17	0.26	0.28	22.07	20.20	19.09	22.45	21.34	19.52
300	0.21	0.31	0.33	27.42	27.50	27.87	28.02	29.73	29.10
400	0.30	0.43	0.48	24.25	23.85	22.40	24.40	24.29	22.61
460	0.42	0.57	0.63	19.01	19.16	18.77	19.30	20.12	19.35
470	0.44	0.60	0.66	18.62	18.78	18.52	18.98	19.84	19.19
480	0.47	0.63	0.69	18.29	18.44	18.30	18.69	19.57	19.04
490	0.49	0.65	0.72	17.97	18.10	18.06	18.39	19.26	18.83
500	0.51	0.68	0.75	17.64	17.74	17.79	18.04	18.84	18.51
505	0.53	0.70	0.77	17.46	17.53	17.64	17.84	18.61	18.32
510	0.54	0.72	0.79	17.27	17.32	17.46	17.61	18.34	18.10
520	0.58	0.76	0.84	16.80	16.81	17.01	17.10	17.72	17.55
640	6.47	7.09	7.60	2.28	2.38	2.40	2.24	2.34	2.37
680	13.57	14.20	14.81	0.80	0.95	1.04	0.79	0.96	1.05
700	17.44	18.04	18.66	0.57	0.71	0.80	0.57	0.74	0.82
720	21.26	21.83	22.46	0.45	0.59	0.67	0.46	0.62	0.70
780	32.01	32.37	33.04	0.28	0.39	0.46	0.32	0.49	0.52
800	35.05	35.24	35.98	0.26	0.36	0.43	0.30	0.48	0.50
850	41.28	40.67	41.75	0.23	0.31	0.37	0.27	0.45	0.45
900	44.32	42.70	44.26	0.20	0.27	0.32	0.26	0.45	0.43
980	45.14	42.67	44.62	0.18	0.24	0.28	0.25	0.45	0.41
1070	44.09	41.36	43.48	0.15	0.22	0.25	0.25	0.46	0.40
1100	43.71	40.92	43.15	0.15	0.21	0.25	0.24	0.46	0.40
1200	42.60	39.83	42.16	0.14	0.21	0.24	0.23	0.47	0.40
1300	43.63	40.34	43.16	0.13	0.20	0.24	0.23	0.48	0.41
1400	44.87	40.86	44.62	0.13	0.21	0.25	0.22	0.50	0.43
1430	46.39	41.45	45.98	0.13	0.22	0.26	0.22	0.49	0.42
1500	61.22	46.35	58.44	0.14	0.24	0.28	0.24	0.52	0.46
1600	40.19	42.74	39.72	0.16	0.28	0.33	0.27	0.56	0.51
1675	31.79	32.50	31.05	0.18	0.33	0.39	0.31	0.60	0.57
1700	29.19	29.60	28.36	0.21	0.36	0.43	0.34	0.63	0.62
1800	16.01	15.41	14.43	0.58	1.01	1.14	0.97	1.49	1.82
1900	12.33	13.78	14.17	0.78	0.80	0.87	1.20	1.64	1.40
2000	18.91	19.39	19.62	0.34	0.47	0.60	0.45	0.91	0.84
2100	21.71	21.95	22.16	0.31	0.46	0.61	0.40	0.82	0.80
2200	24.04	24.23	24.44	0.34	0.50	0.67	0.40	0.81	0.82
2300	26.73	26.95	27.24	0.34	0.51	0.69	0.41	0.80	0.84
2400	31.22	31.55	31.98	0.35	0.53	0.72	0.42	0.78	0.86
2500	43.25	44.63	46.35	0.38	0.58	0.78	0.45	0.79	0.91
2600	28.09	25.84	23.63	0.75	1.09	1.52	0.74	1.14	1.45
2700	8.02	9.01	9.68	2.21	2.14	2.09	2.05	2.11	2.14
2800	5.39	5.65	5.73	2.26	2.71	2.92	2.75	3.24	3.62
2900	2.17	2.63	2.71	6.73	7.17	7.59	10.16	11.59	12.79
3000	2.28	2.90	3.12	7.05	6.76	6.89	9.49	10.23	9.32

REV. X2
SALF-490+
101024
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Low Pass Filter

SALF-490+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
0.1	0.65	0.74	0.78
1	1.02	1.02	1.03
10	1.04	1.05	1.05
20	1.03	1.04	1.04
30	1.03	1.04	1.04
40	1.03	1.03	1.04
50	1.03	1.03	1.03
60	1.03	1.03	1.03
70	1.03	1.03	1.04
80	1.03	1.03	1.04
90	1.04	1.04	1.04
100	1.04	1.04	1.04
200	1.12	1.11	1.11
300	1.27	1.28	1.28
400	1.54	1.55	1.55
460	1.82	1.82	1.83
470	1.87	1.88	1.89
480	1.94	1.95	1.96
490	2.02	2.03	2.05
500	2.11	2.12	2.14
505	2.16	2.18	2.20
510	2.21	2.23	2.25
520	2.33	2.34	2.37
640	3.61	3.48	3.41
680	2.47	2.41	2.33
700	1.99	1.96	1.90
710	1.85	1.81	1.76
720	1.68	1.66	1.59
730	1.51	1.51	1.46
740	1.41	1.42	1.38
750	1.32	1.34	1.30
760	1.21	1.25	1.23
770	1.14	1.18	1.14
780	0.99	1.04	1.04
790	1.00	1.08	1.07
800	1.02	1.11	1.11
810	0.96	1.09	1.11
820	0.95	1.06	1.06
830	0.87	1.01	1.07
840	0.88	1.02	1.12
850	0.85	0.99	1.02
860	0.67	0.83	0.85
870	0.74	0.86	0.93
880	0.88	0.98	1.03
890	0.79	0.89	0.96
892	0.79	0.89	0.93
893	0.79	0.88	0.94
894	0.77	0.89	0.92
895	0.77	0.88	0.94
896	0.73	0.88	0.92
897	0.76	0.83	0.93
898	0.75	0.82	0.87
899	0.69	0.96	1.01
900	0.56	1.08	1.06

REV. X2
SALF-490+
101024
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

