Surface Mount Directional Coupler 75Ω 25dB 5 to 1250 MHz

. 011

Features

- wideband, 5-1250 MHz
- low mainline loss, 0.3 dB typ.
- high coupling, 25 dB typ.
 excellent VSWR, 1.2:1 typ.
- aqueous washable
- protected by U.S Patents 6,133,525 & 6,140,887

Applications

cable tv





CASE STYLE: CD636

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

	Available Tape and Reel at no extra cost
Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range		5		1250	MHz	
Mainline Loss ¹	5 - 870	—	0.3	0.6	dD	
	870- 1250	_	0.5	0.8	dB	
Coupling	5 - 1250	—	25±1.0	—	dB	
Coupling Flatness (±)	5 - 870	_	0.8	1.2	dB	
	5 - 1250	_	1.0	1.85		
Directivity	5 - 870	13	20	—	dB	
	870 - 1250	9	16	_		
Poturn Loop (Input)	5 - 870	18	26	—	dB	
Return Loss (Input)	870 - 1250	13	20	—		
Return Loss (Output)	5 - 870	18	26	—	dB	
	870 - 1250	13	21	_		
Return Loss (Coupling)	5 - 870	18	25	_	dB	
	870 - 1250	13	20	_		
Input Power	5 - 1250	-	_	0.5	W	

1. Mainline loss includes theoretical power loss at coupled port.

Maximum Ratings


Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

Function	Pin Number				
INPUT	1				
OUTPUT	6				
COUPLED	3				
GROUND	2				
75Ω TERM EXTERNAL	4				
ISOLATE (DO NOT USE)	5				


Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.


REV. B M151462 ED-6928A/4 ADC-25-4-75+ DY/CP/AM 150604 Page 1 of 2


ADC-25-4-75+



Outline Dimensions (inch)


	× 110					
G .100	F .055	E .162	D .100	C .220	B .310	A .272
2.54	1.40	4.11	2.54	5.59	7.87	6.91
wt grams 0.25			L .300 7.62	К .065 1.65	J .026 0.66	H .030 0.76





Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
5	0.20	26.47	24.01	24.61	24.69	24.13
10	0.24	26.49	27.07	29.33	29.53	28.40
50	0.22	26.52	30.21	36.63	37.42	33.85
100	0.22	26.51	29.99	41.35	42.23	33.94
200	0.23	26.40	29.24	45.43	52.07	29.90
450	0.28	25.84	30.08	38.12	38.27	23.27
600	0.33	25.49	25.24	36.57	35.32	21.45
850	0.43	25.20	16.94	30.14	39.94	19.97
1000	0.48	25.00	14.65	24.82	31.40	19.81
1250	0.53	24.64	12.11	18.04	21.66	20.40



Additional Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

