# Surface Mount Directional Coupler

### 75Ω 8dB 5 to 1250 MHz

#### Features

- wideband, 5-1250 MHz
- $\bullet$  excellent coupling flatness,  $\pm 0.15$  typ.
- aqueous washable
- protected by U.S Patents 6,133,525 & 6,140,887

#### Applications

- cable tv
- communications

## ADC-8-4-75+



Generic photo used for illustration purposes only CASE STYLE: CD542

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

	Available Tape and Reel at no extra cost
Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000

#### Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range		5		1250	MHz	
Mainline Loss <sup>1</sup>	5 - 870	—	1.8	2.3	dB	
	870 - 1250	- 2.		2.6	dB	
Coupling	5 - 1250	—	7.9±0.5	—	dB	
Coupling Flatness (±)	5 - 1000	—	0.15	0.5	dB	
	5 - 1250	_	0.25	0.7		
Directivity	5 - 500	14	16	—		
	500 - 870	12	15	_	dB	
	870 - 1250	9	13	_		
Return Loss (Input)	5 - 50	13	15	—	dB	
	50 - 1250	14	16	_		
Return Loss (Output)	5 - 50	17	22	—	dB	
	50 -1250	15	18	_		
Return Loss (Coupling)	5 - 50	13	15	—	dB	
	50 - 1250	14	16	_		
Input Power	5 - 1250	_	_	1.0	W	

1. Mainline loss includes theoretical power loss at coupled port.

#### **Maximum Ratings**


Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

#### **Pin Connections**

Function	Pin Number		
INPUT	1		
OUTPUT	6		
COUPLED	3		
GROUND	2		
75Ω TERM EXTERNAL	4		
ISOLATE (DO NOT USE)	5		


#### **Electrical Schematic**



\* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.

REV. G M151462 ED-6621 ADC-8-4-75+ WP/CP/AM 200414 Page 1 of 2

## ADC-8-4-75+




Suggested Layout, Tolerance to be within ±.002

#### Outline Dimensions (inch)

G .100 2.54	F .055 1.40	E .112 2.84	D .100 2.54	C .220 5.59	B .310 7.87	A .272 6.91
wt grams 0.20			L .300 7.62	<b>K</b> .065 1.65	J .026 0.66	H .030 0.76

Demo Board MCL P/N: TB-08 Suggested PCB Layout (PL-042)




.047 TYP

PIN 1

#### **Typical Performance Data**

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
	In-Out			In	Out	Cpl
5	1.68	7.93	18.08	16.44	24.73	16.74
50	1.62	7.93	18.04	17.46	48.30	17.40
100	1.61	7.95	17.94	17.88	37.55	17.69
200	1.62	7.96	17.57	18.31	30.71	18.21
350	1.63	7.95	16.88	19.05	25.93	18.74
500	1.68	7.91	16.23	19.24	22.20	19.64
650	1.75	7.87	15.57	19.53	20.67	20.47
800	1.85	7.84	15.40	19.94	20.98	20.94
1000	2.01	7.80	15.26	21.04	21.74	21.44
1250	2.34	7.84	14.01	23.65	23.57	19.88



#### **Additional Notes**

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

