

Non-Catalog Model

Frequency Mixer

ASK-2

Level 7 (LO Power +7 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : W38

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	1		1000	MHz
	RF (fL to fU)	1		1000	MHz
	IF	0		1000	MHz
Conversion Loss	mid band		6.8	8.0	dB
	Total Range			9.8	dB
LO-RF Isolation	Low Range	40	60		dB
	Mid Range	18	35		dB
	Upper Range	16	26		dB
LO-IF Isolation	Low Range	30	50		dB
	Mid Range	17	25		dB
	Upper Range	10	15		dB
1 dB Comp. Input Power			+1		dBm

Notes: Low Range = [fL to 10fL]
mid band = [2fL to fU/2]

Mid Range = [10fL to fU/2]

Upper Range = [fU/2 to fU]

Non-hermetic

ASK plug-in mounting case X65

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

PIN CONNECTIONS	
LO	1
RF	4
IF	5
GROUND	2, 3, 6

Electrical Schematics

