

Ceramic


# Bandpass Filter

**BFCN-2500+**

50Ω    2100 to 2900 MHz

## The Big Deal

- LTCC construction
- Temperature stable from -55 to +100°C
- Small size (0.126 x .063 X .037")



CASE STYLE: FV1206-4

## Product Overview

The BFCN-2500+ LTCC bandpass filter covers the 2100 to 2900 MHz passband with 2 dB passband insertion loss and 20 dB upper/lower stopband rejection. This model handles up to 2.5W RF input power and provides a wide operating temperature range from -55 to +100°C. Utilizing LTCC multi-layer construction, the filter achieves excellent repeatability of performance and comes in a tiny 1206 ceramic package with wraparound terminations, minimizing performance variations due to parasitics and saving space in dense PCB layouts.


## Key Features

| Feature   | Advantages   |
|---|--|
| LTCC Construction                               | Provides a rugged package well suited for tough environments such as high humidity and temperature extremes. |
| Tiny size (0.126 x .063 x .037")                | Saves space in dense circuit boards and minimizes the effects of parasitics.                                 |
| Wrap-around terminations                        | Provides excellent solderability and easy visual inspection  |
| Wide operating temperature range, -55 to +100°C | Enables reliable performance in extreme environments   |

# Ceramic Bandpass Filter

50Ω 2100 to 2900 MHz

## BFCN-2500+



Generic photo used for illustration purposes only

CASE STYLE: FV1206-4

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

Available Tape and Reel at no extra cost

|           |                                   |
|-----------|-----------------------------------|
| Reel Size | Devices/Reel                      |
| 7"        | 20, 50, 100, 200, 500, 1000, 3000 |



### Features

- Good VSWR, 1.8:1 typ. @ passband
- Small size(0.126 x .063 x .037)
- Temperature stable
- LTCC construction


### Applications

- Harmonic rejection
- Transmitters / Receivers

### Specification Definition



### Top View



### Pad Connections

|        |     |
|--------|-----|
| Input  | 1   |
| Output | 3   |
| Ground | 2,4 |

### Electrical Specifications<sup>1,2</sup> at 25°C

| Parameter        | F#               | Frequency (MHz) | Min.        | Typ. | Max. | Unit |
|------------------|------------------|-----------------|-------------|------|------|------|
| Pass Band        | Center Frequency | —               | —           | 2500 | —    | MHz  |
|                  | Insertion Loss   | F1 - F2         | 2100 - 2900 | —    | 2    | dB   |
|                  | VSWR             | F1 - F2         | 2100 - 2900 | —    | 1.8  | 2.6  |
| Stop Band, Lower | Insertion Loss   | DC - F3         | 1600        | —    | 20   | dB   |
|                  | VSWR             | DC - F3         | 1600        | —    | 20   | :1   |
| Stop Band, Upper | Insertion Loss   | F4 - F5         | 3700 - 5200 | —    | 20   | dB   |
|                  | VSWR             | F4 - F5         | 3700 - 5200 | —    | 15   | :1   |





1. Measured on Mini-Circuits Characterization Test Board TB-824+.

2. This filter is not intended for use as a DC Blocking circuit element. In Application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port.

### Maximum Ratings

|                       |                 |
|-----------------------|-----------------|
| Operating Temperature | -55°C to +100°C |
| Storage Temperature   | -55°C to +100°C |
| RF Power Input*       | 2.5W at 25°C    |

\*Passband rating, derate linearly to 0.7W at 100°C ambient  
Permanent damage may occur if any of these limits are exceeded.



### Full Band Performance

### Pass Band Performance


| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) | Frequency (MHz) | Insertion Loss (dB) | Group Delay (nsec) |
|-----------------|---------------------|-----------|-----------------|---------------------|--------------------|
| 10              | 58.18               | 79.99     | 2100            | 1.88                | 0.90               |
| 40              | 84.01               | 78.80     | 2150            | 1.70                | 0.81               |
| 100             | 69.04               | 74.42     | 2200            | 1.63                | 0.73               |
| 400             | 45.88               | 61.11     | 2250            | 1.60                | 0.66               |
| 1000            | 34.16               | 43.74     | 2300            | 1.60                | 0.62               |
| 1500            | 33.62               | 29.10     | 2320            | 1.60                | 0.59               |
| 2100            | 1.88                | 1.20      | 2340            | 1.60                | 0.58               |
| 2500            | 1.65                | 1.53      | 2360            | 1.61                | 0.57               |
| 2900            | 2.41                | 2.16      | 2380            | 1.61                | 0.57               |
| 3400            | 4.69                | 1.76      | 2400            | 1.62                | 0.56               |
| 3800            | 27.88               | 14.98     | 2500            | 1.65                | 0.55               |
| 4200            | 39.01               | 20.59     | 2600            | 1.74                | 0.54               |
| 4600            | 33.90               | 20.73     | 2700            | 1.89                | 0.54               |
| 5000            | 42.09               | 11.56     | 2800            | 2.11                | 0.54               |
| 5200            | 28.75               | 6.04      | 2900            | 2.41                | 0.55               |

### Pad Connections

|        |     |
|--------|-----|
| Input  | 1   |
| Output | 3   |
| Ground | 2,4 |

### Product Marking: MW


### Outline Drawing



### Outline Dimensions (inch mm)

|      |      |      |      |      |      |      |      |       |  |
|------|------|------|------|------|------|------|------|-------|--|
| A    | B    | C    | D    | E    | F    | G    | H    | J     |  |
| .126 | .063 | .037 | .026 | .075 | .012 | .182 | .104 | .069  |  |
| 3.20 | 1.60 | 0.94 | 0.66 | 1.91 | 0.30 | 4.62 | 2.64 | 1.75  |  |
| K    | L    | M    | N    | P    | Q    | R    |      | wt    |  |
| .119 | .041 | .039 | .013 | .024 | .020 | .039 |      | grams |  |
| 3.02 | 1.04 | 0.99 | 0.33 | 0.61 | 0.51 | 0.99 |      | .020  |  |

### Demo Board MCL P/N: TB-824+ Suggested PCB Layout (PL-454)



### NOTES:

- TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .0066"±.0007". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

### NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)