

Surface Mount Band Pass Filter

SXBP-EDU2058

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	51.30	0.05	65.0	48.00
26.5	29.64	0.11	65.5	43.54
38.5	44.65	0.29	66.0	39.91
50.6	31.80	0.92	66.5	36.89
56.0	44.09	1.82	67.0	34.35
58.0	34.55	2.53	68.0	30.30
62.5	3.52	13.24	70.0	24.59
65.0	1.73	24.57	73.0	20.35
73.0	1.00	21.35	78.0	15.89
93.0	0.81	18.52	87.0	12.31
110.0	0.94	26.85	95.0	11.20
114.0	1.05	41.38	100.0	11.11
120.0	1.35	23.35	105.0	11.47
138.0	19.77	1.95	109.0	11.99
140.0	26.66	1.59	110.0	12.08
154.0	30.35	0.87	111.0	12.48
169.0	43.95	0.71	113.0	13.01
210.0	28.87	0.65	115.5	13.85
770.0	67.47	0.55	116.0	14.04
800.0	80.37	0.57	117.0	14.49
950.0	86.03	0.63	118.0	14.95
1020.0	50.20	0.67	119.0	15.51
3000.0	40.31	3.56	119.5	15.84
5500.0	28.02	4.67	120.0	16.18



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



The Design Engineers Search Engine

IF/RF MICROWAVE COMPONENTS

REV. X1
SXBP-EDU2058
URJ
151130
Page 1 of 1