

Surface Mount High Pass Filter

SXHP-EDU1981

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.30	88.98	0.01	3	360.24
0.60	79.54	0.01	4	146.10
0.90	61.89	0.02	5	73.93
1.00	57.37	0.03	6	59.95
1.20	49.81	0.05	7	44.01
1.38	44.54	0.07	8	32.34
1.80	40.78	0.20	9	24.89
1.90	48.83	0.25	10	19.82
2.00	38.25	0.32	11	16.21
2.04	32.99	0.36	12	13.53
2.06	30.81	0.39	13	11.45
2.18	20.56	0.60	14	9.84
2.50	3.13	6.33	15	8.57
2.55	2.08	9.48	16	7.52
3.00	0.68	17.87	17	6.67
5.00	0.27	38.87	18	5.96
7.00	0.22	29.97	19	5.35
10.00	0.19	27.02	20	4.85
15.00	0.16	27.60	21	4.41
30.00	0.15	30.09	23	3.70
100.00	0.20	29.45	24	3.42
200.00	0.24	24.79	26	2.94
300.00	0.30	21.17	28	2.57
400.00	0.41	18.00	30	2.26



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. X1
SXHP-EDU1981
URJ
151215
Page 1 of 1