# **Bandpass Filter**

BFTC-618+

 $50\Omega$ 460 to 776 MHz

# The Big Deal

- LTCC construction
- Temperature stable from -40°C to +85°C
- Small size (0.150 x 0.150 x 0.059")



Generic photo used for illustration purposes only CASE STYLE: FR933-1

## **Product Overview**

The BFTC-618+ LTCC bandpass filter covers the 460 to 776 MHz passband with 25 dB upper/lower stopband rejection. This model handles up to 3W RF input power and provides a wide operating temperature range from -40 to +85°C. Utilizing LTCC multi-layer construction, the filter achieves excellent repeatability of performance and comes in a tiny ceramic package saving space in dense PCB layouts.

# **Key Features**

Feature	Advantages			
LTCC Construction	Provides a rugged package well suited for tough environments such as high humidity and temperature extremes.			
Tiny size (0.150 x 0.150 x 0.059")	Saves space in dense circuit boards and minimizes the effects of parasitics.			
Wide operating temperature range, -40 to +85°C	Enables reliable performance in extreme environments			

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



# **Bandpass Filter**

 $50\Omega$ 460 to 776 MHz

# **BFTC-618+**



Generic photo used for illustration purposes only CASE STYLE: FR933-1

### Electrical Specifications<sup>1,2</sup> at 25°C

Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	_	_	_	618	_	MHz
Pass Band	Insertion Loss	F1-F2	460-776	_	4.8	6.0	dB
	VSWR	F1-F2	460-776	_	1.3	-	:1
Stop Band, Lower	Insertion Loss	F3-F4	1-330	25	35	_	dB
	VSWR	F3-F4	1-330	_	16	-	:1
Stop Band, Upper	Insertion Loss	F5-F6	980-2400	25	30	_	dB
Stop Ballu, Opper	VSWR	F5-F6	980-2400	_	10	_	:1

- 1. Measured on Mini-Circuits Characterization Test Board TB-233
- 2. This filter is not intended for use as a DC Blocking circuit element. In Application where DC voltage is present at either input or output ports, blocking capacitors are required at the corresponding RF port.

Maximum Ratings					
Operating Temperature	-40°C to 85°C				
Storage Temperature	-55°C to 100°C				
RF Power Input*	3 W max @ +25°C				

\*Passband rating, derate linearly to 1.5 W at 85°C ambient Permanent damage may occur if any of these limits are exceeded


#### **Features**

- · Good VSWR 1.5 typ. @ passband
- Small size
- · Hermetically sealed
- Temperature sable
- · LTCC construction


#### **Applications**

- Test and measurement
- · Harmonic rejection
- Transmitters / Receivers

#### **Functional Schematic**




#### **Typical Frequency Response**





+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


### Typical Performance Data at 25°C

Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
80.59	8168.80	460	5.88
60.35	4270.56	468	5.46
41.68	101.99	470	5.38
46.00	13.65	480	4.90
40.52	10.57	490	4.47
35.92	9.90	500	4.12
31.96	9.26	510	3.88
21.77	7.32	550	3.25
4.36	1.81	570	3.08
3.52	1.43	580	3.00
2.03	1.21	600	2.89
3.33	1.12	618	2.83
4.16	1.34	620	2.85
13.10	3.87	650	2.79
20.31	5.33	680	2.83
29.80	6.86	700	2.88
38.66	8.06	720	3.00
34.46	35.78	740	3.16
51.21	47.51	760	3.40
32.85	51.96	776	3.66
	80.59 60.35 41.68 46.00 40.52 35.92 31.96 21.77 4.36 3.52 2.03 3.33 4.16 13.10 20.31 29.80 38.66 34.46 51.21	Insertion Loss (dB)	Insertion Loss (dB)










Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

#### **Pad Connections**

RF IN	2
RF OUT	5
GROUND	1,3,4,6

**Product Marking: 351** 

Demo Board MCL P/N: TB-233 Suggested PCB Layout (PL-112)




NOTES: 1.TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020"  $\pm$  0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2.BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER


MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

#### **Outline Drawing**



#### PCB Land Pattern



Suggeested Layout, Tolerance to be within±.002

#### Outline Dimensions (inch )

Α	В	С	D	Ε	F	G	Н
.150	.150	.059			.035	.028	
3.81	3.81	1.50			.89	.71	
.1	K	L	М	N	Р		Wt.
.060		.184			-		grams
1.52	76	4.67	1 27	1 01	1 12		0.15

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp