Surface Mount Directional Coupler

DBTC-17-5LX+

 50Ω , 17dB coupling, 50 to 2000 MHz

Features

- · very flat coupling
- · very broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- · leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

Generic photo used for illustration purposes only CASE STYLE: AT1642

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost						
Reel Size	Devices/Reel					
7"	20, 50, 100, 200, 500					
13"	1000, 2000					

Applications

- cellular
- PCS
- DECT/PHS
- GSM

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit
Frequency Range		5		1500	MHz
	50-1000		0.9	1.4	
Mainline Loss ¹	1000-1500		1.0	1.5	dB
	1500-2000		1.1	1.6	
	50-1000		17.0±0.7		
Nominal Coupling	1000-1500		17.2±0.9		dB
	1500-2000		17.0±1.0		
	50-1000			±0.9	
Coupling Flatness(±)	1000-1500			±1.0	dB
	1500-2000			±0.8	
Directivity	50-1000	13	20		
	1000-1500	10	20		dB
	1500-2000	_	14		
VSWR ²	50-1000		1.2		
	1000-1500		1.2		dB
	1500-2000		1.2		
	50-1000			2.0	
Input Power	1000-1500			2.0	W
	1500-2000			2.0	1

^{1.} Includes theoretical coupled power loss of 0.07 dB at 17 dB coupling.

Maximum Ratings

Parameter	Ratings		
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

Function	Pin Number			
INPUT	3			
OUTPUT	4			
COUPLED	1			
GROUND	2			
ISOLATE (DO NOT USE)	6			

Product Marking



Electrical Schematic



 ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THA POLITES DC FROM RF PORTS TO GROUND




REV. A M151107 ED-8784A/4 DBTC-17-5LX+ WP/CP/AM 190821

^{2.} For coupled port VSWR above 500 MHz, 1.6:1 typ.

DBTC-17-5LX+


Outline Drawing



Outline Dimensions (inch)


F	Е	D	С	В	Α
.025	.037	.050	.155	.150	.166
0.64	0.94	1.27	3.94	3.81	4.22
wt	L	K	J	Н	G
grams	.004	.030	.184	.060	.012
0.10	0.10	0.76	4.67	1.52	0.30


Demo Board MCL P/N: TB-278 Suggested PCB Layout (PL-150) X Ø.015 PTH FOR CROUND \



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.








DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)	Directivity (dB)	Return Loss (dB)		
	In-Out	In-Cpl		In	Out	Cpl
50.00	0.64	16.41	15.92	23.43	27.62	18.46
100.00	0.66	16.42	16.17	23.56	27.75	18.62
500.00	0.76	16.74	18.53	22.36	23.13	18.78
800.00	0.85	17.06	22.42	21.45	21.80	18.22
1000.00	0.91	17.30	22.32	21.67	21.94	17.08
1300.00	0.99	17.63	17.74	22.81	22.71	14.85
1500.00	1.05	17.81	15.41	24.84	24.12	13.40
1600.00	1.08	17.88	14.43	25.91	24.48	12.71
1900.00	1.18	18.07	12.20	28.04	25.71	10.95
2000.00	1.21	18.11	11.55	28.07	25.97	10.50







Additional Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp