# Surface Mount Directional Coupler 5 to 1000 MHz

#### 9dB coupling, 50Ω.

#### **Features**

- · very flat coupling · very broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- · leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

#### Applications

- VHF/UHF receivers/transmitters
- cellular

#### Electrical Specifications at 25°C

| Parameter            | Condition (MHz) | Min. | Тур.    | Max. | Unit |
|----------------------|-----------------|------|---------|------|------|
| Frequency Range      |                 | 5    |         | 1000 | MHz  |
|                      | 5-50            |      | 1.2     | 2.0  |      |
| Mainline Loss        | 50-500          |      | 1.2     | 1.8  | dB   |
|                      | 500-1000        |      | 1.5     | 2.0  |      |
| Nominal Coupling     | 5-1000          |      | 9.0±0.5 |      | dB   |
| Coupling Flatness(±) | 5-1000          |      |         | ±0.5 | dB   |
|                      | 5-50            | 17   | 21      |      |      |
| Directivity          | 50-500          | 13   | 18      |      | dB   |
|                      | 500-1000        | _    | 15      |      |      |
| VSWR                 | 5-1000          |      | 1.2     |      | dB   |
|                      | 5-50            |      |         | 0.5  |      |
| Input Power          | 50-500          |      |         | 1.0  | W    |
|                      | 500-1000        |      |         | 1.0  |      |

1. Includes theoretical coupled power loss of 0.58 dB at 9 dB coupling

2. For coupled port VSWR above 500 MHz, 1.6:1 typ.

#### Maximum Ratings

| Parameter             | Ratings        |  |  |
|-----------------------|----------------|--|--|
| Operating Temperature | -40°C to 85°C  |  |  |
| Storage Temperature   | -55°C to 100°C |  |  |

Permanent damage may occur if any of these limits are exceeded.


#### **Product Marking**



## **Pin Connections**

| Function             | Pin Number |  |  |
|----------------------|------------|--|--|
| INPUT                | 3          |  |  |
| OUTPUT               | 4          |  |  |
| COUPLED              | 1          |  |  |
| GROUND               | 2          |  |  |
| ISOLATE (DO NOT USE) | 6          |  |  |

## **Electrical Schematic**





REV. A M151107 ED-8958A/1 DBTC-9-4LX+ DY/RS/CP/AM 190828 Page 1 of 2

# DBTC-9-4LX+




Generic photo used for illustration purposes only CASE STYLE: AT1642

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

|           | Available Tape and Reel<br>at no extra cost |
|-----------|---------------------------------------------|
| Reel Size | Devices/Reel                                |
| 7"        | 20, 50, 100, 200, 500                       |
| 13"       | 1000, 2000                                  |


**Mini-Circuits** www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

## DBTC-9-4LX+



#### **Typical Performance Data**

| Frequency<br>(MHz) | Mainline Loss<br>(dB) | Coupling<br>(dB) | Directivity<br>(dB) | Return Loss<br>(dB) |       |       |
|--------------------|-----------------------|------------------|---------------------|---------------------|-------|-------|
| ()                 | In-Out                | In-Cpl           | ()                  | In                  | Out   | Cpl   |
| 5.00               | 1.18                  | 8.93             | 21.62               | 17.90               | 24.67 | 18.40 |
| 10.00              | 1.10                  | 8.89             | 21.70               | 19.15               | 29.04 | 19.50 |
| 50.00              | 1.07                  | 8.87             | 21.50               | 20.07               | 32.70 | 20.22 |
| 100.00             | 1.09                  | 8.90             | 20.99               | 20.12               | 31.81 | 20.27 |
| 300.00             | 1.16                  | 8.93             | 19.47               | 20.49               | 30.43 | 18.93 |
| 500.00             | 1.20                  | 8.90             | 17.60               | 21.02               | 30.62 | 16.66 |
| 600.00             | 1.23                  | 8.88             | 16.50               | 20.89               | 30.39 | 15.36 |
| 800.00             | 1.31                  | 8.86             | 14.74               | 20.45               | 30.31 | 12.91 |
| 900.00             | 1.37                  | 8.85             | 14.07               | 20.06               | 29.26 | 11.86 |
| 1000.00            | 1.43                  | 8.86             | 13.44               | 19.34               | 27.16 | 10.86 |



#### **Additional Notes**

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

