

Frequency Synthesizer

DSN-2036A-119+

50Ω 924 to 2036 MHz

The Big Deal

- Fractional N synthesizer
- Low phase noise and spurious
- Wide bandwidth



CASE STYLE: KL1294

Product Overview

The DSN-2036A-119+ is a Frequency Synthesizer, designed to operate from 924 to 2036 MHz for Digital TV distribution application. The DSN-2036A-119+ is packaged in a metal case (size of 1.250" x 1.000" x 0.232") to shield against unwanted signals and noise.

Key Features

Feature	Advantages
Low phase noise and spurious: <ul style="list-style-type: none">• Phase Noise: -97 dBc/Hz typ. @ 10 kHz offset• Step Size Spurious: -70 dBc typ.• Comparison Spurious: -85 dBc typ.• Reference Spurious: -85 dBc typ.	Low phase noise and spurious improve system EVM (Error Vector Magnitude).
Robust design and construction	To enhance the robustness of DSN-2036A-119+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount

Frequency Synthesizer

DSN-2036A-119+

50Ω 924 to 2036 MHz



CASE STYLE: KL1294

Features

- Fractional N synthesizer
- Integrated VCO + PLL
- Low phase noise and spurious
- Robust design and construction
- Operating voltage (VCC VCO=+8V, VCC PLL=+18V)
- Wide bandwidth

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Applications

- Digital TV distribution

General Description

The DSN-2036A-119+ is a Frequency Synthesizer, designed to operate from 924 to 2036 MHz for Digital TV distribution application. The DSN-2036A-119+ is packaged in a metal case (size of 1.250" x 1.000" x 0.232") to shield against unwanted signals and noise. To enhance the robustness of DSN-2036A-119+, each internal component is secured to the substrate with chip bonder, thereby eliminating the risk of tombstoning during subsequent solder reflow operations by the customer.

Simplified Schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Electrical Specifications (over operating temperature -20°C to +70°C)

Parameters	Test Conditions	Min.	Typ.	Max.	Units	
Frequency Range	-	924	-	2036	MHz	
Step Size	-	-	250	-	kHz	
Comparison Frequency	-	-	20	-	MHz	
Settling Time	Within ± 1 kHz	-	10	-	mSec	
Output Power	-	-1.5	+1.5	+4.5	dBm	
SSB Phase Noise	@ 100 Hz offset	-	-80	-	dBc/Hz	
	@ 1 kHz offset	-	-100	-92		
	@ 10 kHz offset	-	-97	-91		
	@ 100 kHz offset	-	-115	-109		
	@ 1 MHz offset	-	-138	-132		
Step Size Spurious Suppression	Step Size 250 kHz	-	-70	-50	dBc	
0.5 Step Size Spurious Suppression	0.5 Step Size 125 kHz	-	-70	-50		
Reference Spurious Suppression	Ref. Freq. 10 MHz	-	-85	-70		
Comparison Spurious Suppression	Comp. Freq. 20 MHz	-	-85	-70		
Non - Harmonic Spurious Suppression	-	-	-90	-		
Harmonic Suppression	-	-	-25	-8		
VCO Supply Voltage	+8.0	+7.6	+8.0	+8.4	V	
PLL Supply Voltage	+18.0	+17.5	+18.0	+18.5	V	
VCO Supply Current	-	-	51	57	mA	
PLL Supply Current	-	-	23	32		
Reference Input (External)	Frequency	10 (square wave)	-	10	MHz	
	Amplitude	1	-	1	V _{P-P}	
	Input impedance	-	-	100	KΩ	
	Phase Noise @ 1 kHz offset	-	-	-145	dBc/Hz	
RF Output port Impedance	-	-	50	-	Ω	
Input Logic Level	Input high voltage	-	2.65	-	V	
	Input low voltage	-	-	0.65	V	
Digital Lock Detect	Locked	-	2.00	-	2.85	V
	Unlocked	-	-	-	0.40	V
Frequency Synthesizer PLL	-	ADF4153				
PLL Programming	-	3-wire serial 3.3V CMOS				
Register Map @ 2036 MHz	R0_Register	-	(MSB) 11001010000010000000 (LSB)			
	R1_Register *	-	(MSB) 10X000100000101000001 (LSB)			
	R2_Register *	-	(MSB) 10YZW0100010 (LSB)			
	R3_Register	-	(MSB) 1111000111 (LSB)			

*** Refer to Charge Pump Settings**

FREQ.LOCK [MHz]	Charge Pump Settings			
	X	Y	Z	W
925.00 - 1070.00	0	0	0	1
1070.25 - 1680.00	0	0	1	0
1680.25 - 1850.00	0	0	1	1
1850.25 - 1966.00	1	1	0	0
1966.25 - 2036.00	1	1	0	1

Absolute Maximum Ratings

Parameters	Ratings
VCO Supply Voltage	9V
PLL Supply Voltage	19V
VCO Supply Voltage to PLL Supply Voltage	N.A
Reference Frequency Voltage	-0.3Vmin, +3.6Vmax
Data, Clock, LE Levels	-0.3Vmin, +3.6Vmax
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

Permanent damage may occur if any of these limits are exceeded

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

FREQUENCY (MHz)	POWER OUTPUT (dBm)			VCO CURRENT (mA)			PLL CURENT (mA)		
	-25°C	+25°C	+75°C	-25°C	+25°C	+75°C	-25°C	+25°C	+75°C
	924	1.68	1.63	1.58	49.26	50.22	50.96	20.99	22.74
976	1.43	1.42	1.42	49.28	50.23	50.95	21.12	22.90	24.40
1100	1.31	1.35	1.40	49.53	50.45	51.14	19.47	21.24	22.74
1224	1.37	1.38	1.38	49.68	50.55	51.24	20.97	22.78	24.33
1348	1.44	1.40	1.32	49.85	50.69	51.34	21.43	23.25	24.83
1472	1.48	1.40	1.23	50.00	50.82	51.48	21.48	23.32	24.91
1596	1.61	1.32	1.31	50.14	50.97	51.63	21.10	22.94	24.54
1720	1.56	1.38	1.25	50.33	51.20	51.87	19.45	21.27	22.86
1844	1.52	1.39	1.22	50.25	51.17	51.90	20.98	22.83	24.45
1968	1.32	1.27	1.10	50.36	51.36	52.16	21.69	23.60	25.28
2036	0.86	1.08	0.91	50.22	51.24	52.09	21.36	23.27	24.95

FREQUENCY (MHz)	HARMONICS (dBc)					
	F2			F3		
	-25°C	+25°C	+75°C	-25°C	+25°C	+75°C
924	-12.76	-13.53	-15.64	-17.11	-18.45	-20.62
976	-15.00	-15.53	-17.77	-16.61	-18.01	-20.63
1100	-21.39	-21.48	-21.89	-16.84	-18.24	-20.87
1224	-32.20	-31.25	-28.66	-20.02	-21.55	-24.03
1348	-32.15	-34.27	-37.49	-23.35	-25.47	-28.03
1472	-25.29	-26.79	-29.03	-26.95	-28.91	-31.18
1596	-22.88	-24.17	-26.68	-31.74	-32.49	-33.80
1720	-23.16	-24.65	-28.00	-40.18	-41.32	-41.26
1844	-26.42	-28.03	-29.39	-43.84	-43.31	-42.70
1968	-34.64	-35.72	-35.40	-40.62	-39.55	-39.54
2036	-44.95	-46.24	-44.99	-37.56	-37.76	-37.02

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	+25°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
924	-87.41	-103.93	-97.71	-113.42	-137.52
976	-86.46	-102.47	-96.48	-113.67	-136.67
1100	-87.03	-101.56	-98.95	-114.34	-138.39
1224	-86.10	-101.86	-98.60	-115.61	-139.42
1348	-85.80	-100.10	-98.27	-116.38	-140.12
1472	-84.69	-99.50	-97.58	-116.52	-141.30
1596	-84.34	-97.65	-96.77	-116.66	-141.54
1720	-85.08	-96.01	-98.00	-116.36	-141.71
1844	-85.09	-97.18	-96.60	-116.94	-141.72
1968	-84.32	-95.91	-97.97	-116.39	-141.20
2036	-83.66	-96.82	-96.88	-116.88	-140.84

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	-25°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
924	-88.88	-104.60	-98.64	-114.03	-138.60
976	-89.32	-101.55	-97.69	-114.27	-138.40
1100	-87.87	-103.57	-99.78	-114.69	-139.22
1224	-86.92	-101.47	-98.94	-116.21	-140.37
1348	-85.43	-101.65	-99.22	-117.01	-141.24
1472	-85.68	-101.73	-98.45	-117.15	-142.21
1596	-84.23	-99.45	-97.63	-117.34	-142.19
1720	-83.38	-99.14	-98.74	-116.86	-142.08
1844	-82.50	-97.44	-97.39	-117.45	-142.31
1968	-82.45	-96.32	-98.38	-116.80	-141.80
2036	-82.16	-95.37	-97.65	-117.03	-141.50

FREQUENCY (MHz)	PHASE NOISE (dBc/Hz) @OFFSETS				
	+75°C				
	100Hz	1kHz	10kHz	100kHz	1MHz
924	-90.31	-101.37	-96.83	-112.42	-135.72
976	-88.65	-100.68	-96.37	-112.97	-135.19
1100	-87.65	-101.34	-98.95	-113.58	-136.97
1224	-87.01	-100.77	-98.76	-114.85	-138.51
1348	-86.99	-101.61	-98.56	-115.55	-139.58
1472	-86.55	-98.54	-96.85	-115.62	-140.18
1596	-85.55	-99.32	-96.34	-115.91	-140.47
1720	-83.87	-99.35	-97.07	-115.53	-140.86
1844	-84.55	-96.51	-96.01	-116.36	-140.90
1968	-83.77	-95.47	-96.63	-116.05	-140.36
2036	-82.20	-96.66	-95.11	-116.51	-140.16

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



COMPARISON SPURIOUS ORDER	COMPARISON SPURIOUS @Fcarrier 924MHz+(n*Fcomparison) (dBc) note 1			COMPARISON SPURIOUS @Fcarrier 1492MHz+(n*Fcomparison) (dBc) note 1			COMPARISON SPURIOUS @Fcarrier 2036MHz+(n*Fcomparison) (dBc) note 1			
	n	-25°C	+25°C	+75°C	-25°C	+25°C	+75°C	-25°C	+25°C	+75°C
	-5	-105.04	-95.38	-98.54	-97.78	-92.31	-100.79	-100.19	-90.97	-91.79
-4	-98.44	-92.13	-94.90	-93.59	-95.52	-93.14	-95.46	-92.43	-90.08	
-3	-99.04	-90.77	-89.26	-86.65	-95.67	-89.71	-97.73	-90.89	-101.28	
-2	-100.08	-91.14	-95.89	-90.95	-94.63	-95.36	-93.38	-90.83	-93.76	
-1	-91.29	-92.88	-86.41	-88.07	-96.14	-100.08	-93.58	-87.79	-90.57	
0 ^{note 2}	-	-	-	-	-	-	-	-	-	
+1	-85.60	-84.89	-88.19	-98.01	-99.69	-93.61	-96.89	-95.58	-96.11	
+2	-88.21	-88.21	-89.76	-99.85	-96.36	-90.75	-98.31	-94.60	-100.32	
+3	-88.99	-87.93	-93.68	-99.10	-98.39	-93.47	-90.77	-96.25	-109.30	
+4	-89.96	-101.80	-95.68	-97.23	-97.05	-90.71	-93.01	-94.11	-95.47	
+5	-92.73	-102.53	-93.69	-95.61	-106.03	-96.02	-96.25	-95.60	-97.52	

Note 1: Comparison frequency 20 MHz
 Note 2: All spurs are referenced to carrier signal (n=0).

REFERENCE SPURIOUS ORDER	REFERENCE SPURIOUS @Fcarrier 924MHz+(n*Freference) (dBc) note 3			REFERENCE SPURIOUS @Fcarrier 1492MHz+(n*Freference) (dBc) note 3			REFERENCE SPURIOUS @Fcarrier 2036MHz+(n*Freference) (dBc) note 3			
	n	-25°C	+25°C	+75°C	-25°C	+25°C	+75°C	-25°C	+25°C	+75°C
	-5	-115.28	-118.59	-110.48	-98.92	-111.95	-101.49	-112.65	-109.74	-110.25
-4	-100.08	-91.14	-95.89	-90.95	-94.63	-95.36	-93.38	-90.83	-93.76	
-3	-115.17	-111.32	-115.54	-99.36	-102.56	-115.50	-105.11	-105.34	-110.89	
-2	-91.29	-92.88	-86.41	-88.07	-96.14	-100.08	-93.58	-87.79	-90.57	
-1	-113.09	-102.27	-111.50	-100.51	-98.99	-99.78	-106.16	-101.05	-108.72	
0 ^{note 4}	-	-	-	-	-	-	-	-	-	
+1	-111.45	-101.41	-112.88	-99.82	-100.96	-101.71	-104.66	-100.15	-108.07	
+2	-85.60	-84.89	-88.19	-98.01	-99.69	-93.61	-96.89	-95.58	-96.11	
+3	-112.34	-110.10	-110.52	-103.79	-108.56	-99.99	-110.12	-109.35	-109.32	
+4	-88.21	-88.21	-89.76	-99.85	-96.36	-90.75	-98.31	-94.60	-100.32	
+5	-106.25	-113.72	-111.97	-100.15	-117.66	-102.23	-110.07	-108.76	-109.52	

Note 3: Reference frequency 10 MHz
 Note 4: All spurs are referenced to carrier signal (n=0).

Notes
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



STEP SIZE SPURIOUS ORDER n	0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 924MHz+(n*Fstep size) (dBc) note 5			0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 1492MHz+(n*Fstep size) (dBc) note 5			0.5 STEP SIZE & STEP SIZE SPURIOUS @Fcarrier 2036MHz+(n*Fstep size) (dBc) note 5		
	-25°C	+25°C	+75°C	-25°C	+25°C	+75°C	-25°C	+25°C	+75°C
-5.0	-108.64	-107.52	-108.69	-105.80	-105.52	-111.77	-107.19	-105.42	-103.37
-4.5	-105.43	-100.33	-110.25	-109.10	-102.01	-99.23	-106.01	-115.40	-109.76
-4.0	-108.39	-98.92	-100.40	-108.60	-114.72	-112.42	-103.01	-106.73	-111.36
-3.5	-96.21	-115.01	-101.37	-101.40	-107.43	-100.53	-107.55	-101.58	-102.13
-3.0	-103.26	-101.49	-100.18	-99.95	-113.47	-110.69	-103.33	-103.85	-107.87
-2.5	-93.82	-88.37	-85.90	-99.34	-98.64	-102.86	-93.22	-91.04	-98.25
-2.0	-106.67	-96.50	-90.80	-100.12	-105.50	-101.11	-93.48	-102.14	-100.18
-1.5	-80.55	-84.50	-85.61	-105.29	-99.35	-93.99	-88.18	-88.74	-104.54
-1.0	-89.71	-95.93	-82.94	-84.62	-87.79	-80.69	-76.83	-83.77	-87.86
-0.5	-69.81	-67.18	-73.35	-78.63	-75.07	-70.63	-64.39	-70.17	-68.90
0 ^{note 6}	-	-	-	-	-	-	-	-	-
+0.5	-69.80	-67.01	-71.90	-80.91	-74.95	-71.49	-65.28	-68.78	-68.04
+1.0	-91.40	-101.35	-84.81	-83.90	-87.14	-80.79	-77.85	-83.63	-87.62
+1.5	-80.07	-84.81	-85.08	-101.96	-101.40	-92.29	-88.97	-88.13	-102.91
+2.0	-109.10	-96.25	-89.88	-98.74	-108.65	-102.75	-95.42	-106.96	-99.89
+2.5	-95.07	-88.56	-86.32	-102.52	-100.24	-100.83	-92.42	-90.68	-96.82
+3.0	-104.69	-103.24	-99.66	-98.72	-111.01	-109.31	-101.20	-103.22	-107.09
+3.5	-97.35	-116.05	-100.45	-100.58	-106.79	-102.43	-103.01	-101.98	-101.10
+4.0	-113.05	-99.15	-98.99	-106.61	-114.54	-109.94	-103.95	-105.03	-110.02
+4.5	-106.50	-100.14	-110.57	-111.09	-100.82	-100.39	-107.04	-116.32	-112.45
+5.0	-107.66	-109.73	-107.10	-110.23	-103.35	-107.46	-103.05	-104.32	-104.62

Note 5: Step size 250 kHz




Note 6: All spurs are referenced to carrier signal (n=0).

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp








Typical Performance Curves



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp











Notes




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp





Notes
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Pin Configuration




Pin Connection

Pin Number	Function	Pin Number	Function
1	GND	12	LE
2	GND	13	GND
3	GND	14	REF IN
4	GND	15	GND
5	RF OUT	16	VCC VCO
6	GND	17	GND
7	LOCK DET	18	VCC PLL
8	GND	19	GND
9	DATA	20	GND
10	GND	21	GND
11	CLOCK	22	GND

Recommended Application Circuit


Note: REF IN and RF OUT ports are internally AC coupled.



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Device Marking**Additional Detailed Technical Information**

Additional information is available on our web site. To access this information enter the model number on our web site home page.

Case Style: KL1294

Tape & Reel: TR-F97

Suggested Layout for PCB Design: PL-318

Evaluation Board: TB-553+

Environment Ratings: ENV03T2

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

